



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton Series C complete molded case circuit breaker

HFD1040

UPC:786679175309

### Dimensions:

- **Height:** 1.38 IN
- **Length:** 3.38 IN
- **Width:** 1.38 IN

**Weight:**4 LB

**Warranties:** No Data

### Specifications:

- **Amperage Rating:** 40A
- **Interrupt Rating:** 100 kAIC at 240 Vac, 65 kAIC at 480 Vac
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 347 Vac, 125 Vdc
- **Trip Type:** Fixed thermal, fixed magnetic
- **Circuit Breaker Type:** HFD
- **Circuit Breaker Frame Type:** Complete breaker
- **Frequency Rating:** 50/60 Hz
- **Series:** Series C
- **Terminals:** Load side
- **Frame:** F-frame

### Supporting documents:

- [Application of Tap Rules to Molded Case Breaker Terminals](#)
- [UL listed 100%-rated molded case circuit breakers](#)
- [Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)
- [Multi-wire lugs product aid](#)
- [Motor protection circuit breakers product aid](#)
- [Power metering and monitoring with Modbus](#)



[RTU product aid](#)

- [StrandAble terminals product aid](#)
- [Circuit breaker motor operators product aid](#)
- [Current limiting Series C molded case circuit breakers product aid](#)
- [MOEM MCCB Product Selection Guide](#)
- [Plug-in adapters for molded case circuit breakers product aid](#)
- [Molded case circuit breakers](#)
- [Eatons Volume 4-Circuit Protection](#)
- [HFD1 2D PDF](#)
- [Time Current Curves for Series C® F-Frame Circuit Breakers](#)
- [F-frame Molded Case Circuit Breaker Drawing](#)
- [HFD1 3D Inventor](#)
- [HFD1 3D Model Xchange](#)
- [HFD1 2D Drawing Xchange](#)
- [Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)
- [Counterfeit and Gray Market Awareness Guide](#)
- [Series C G-Frame molded case circuit breakers time current curves](#)
- [Series C J-Frame molded case circuit breakers time current curves](#)
- [Series C F-Frame molded case circuit breakers](#)
- [MOEM MCCB product selection guide](#)
- [F-Frame 310+ Molded-case circuit breakers 15-225A](#)
- [Breaker service centers](#)

**Certifications:**

- [UL Listed](#)

**Product compliance:** No Data