



Job Name:

Job Type:

Comments:

Quantity:

5231-02: Three-Light Brass Hall/Foyer



Dimensions:

Diameter: 9 1/2"

Height Flush: 15 1/4"

Height: 16"

Overall Height: 53 1/2"

Wire: 144" (color/Gold)

Chain: 36"

Mounting Proc.: Dual Mount

Connection: Mounted To Box

Bulb Appearance: Clear

Bulbs:

3 - Candelabra Torpedo 40w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Fixture is dual mount and may be installed semi-flush or as a pendant.
- Easily converts to LED with optional replacement lamps

Collection: Bretton

Three Light Hall Fixture Finished in Polished Brass with Clear Glass Panes All Around. Fixture Can be Mounted Close to Ceiling or as a Pendant.

Three light Hall/Foyer fixture finished in polished brass with clear glass panes.

UPC #:785652523120

Finish: Polished Brass (02)

Material List:

1 Body - Steel - Polished Brass

1 Chain - Steel - Polished Brass

Safety Listing:

UL Listed for Dry Locations
cUL Listed for Dry Locations

Instruction Sheets:

English (HC-264)
French (F-005)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear	6			4 9/32	9 15/16					

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	5231-02	1	785652523120	10.5	9.75	16	0.948	8.1	100	Yes
NJ Pallet		56		48	40	72	80	448		No
NV Pallet		56		48	40	72	80	448		No



Job Name:

Job Type:

Comments:

Quantity:

5231-782: Three-Light Hall/Foyer



Dimensions:

Diameter: 9 1/2"

Height: 16"

Height Flush: 15 1/4"

Overall Height: 53 1/2"

Wire: 144" (color/Brown)

Chain: 36"

Mounting Proc.: Dual Mount

Connection: Mounted To Box

Bulb Appearance: Clear

Bulbs:

3 - Candelabra B Torpedo 40w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Fixture is dual mount and may be installed semi-flush or as a pendant.
- Easily converts to LED with optional replacement lamps

Collection: Bretton

Three Light Convertible Hall Fixture Finished in Heirloom Bronze with Clear Glass Panes All Around.

Three Light Hall Fixture Finished in Heirloom Bronze with Clear Glass Panels all around. Fixture can be mounted close to ceiling or as a Pendant.

UPC #:785652523175

Finish: Heirloom Bronze (782)

Material List:

1 Body - Steel - Heirloom Bronze

1 Chain - Steel - Heirloom Bronze

Safety Listing:

UL Listed for Dry Locations
cUL Listed for Dry Locations

Instruction Sheets:

English (HC-264)
French (F-005)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear	6			4 9/32	10 1/8					

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	31/32			4 15/16		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frts. Class	UPS Ship
Individual	5231-782	1	785652523175	10.5	9.78	16	0.951	8	100	Yes
NJ Pallet		70		48	40	72	80	560		No
NV Pallet		70		48	40	72	80	560		No



Job Name:

Job Type:

Comments:

Quantity:

5231-962: Three-Light Hall Foyer



Dimensions:

Diameter: 9 1/2"

Height: 16"

Height Flush: 15 1/4"

Overall Height: 53 1/2"

Wire: 144" (color/Clear)

Chain: 36"

Mounting Proc.: Dual Mount

Connection: Mounted To Box

Bulb Appearance: Clear

Bulbs:

3 - Candelabra B Torpedo 40w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Fixture is dual mount and may be installed semi-flush or as a pendant.
- Easily converts to LED with optional replacement lamps

Collection: Bretton

Three Light Convertible Hall Fixture Finished in Brushed Nickel with Clear Glass Panes All Around.

Three Light Hall Fixture Finished in Oxford Bronze with Clear Glass Panels all around. Fixture can be mounted close to ceiling or as a Pendant.

Shown w/ Canterbury & Sussex families.

UPC #:785652523199

Finish: Brushed Nickel (962)

Material List:

1 Body - Steel - Brushed Nickel

1 Chain - Steel - Brushed Nickel

Safety Listing:

UL Listed for Dry Locations
cUL Listed for Dry Locations

Instruction Sheets:

English (HC-264)
French (F-005)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Clear	6			8 3/16	15 25/32					

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	31/32			4 15/16		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	5231-962	1	785652523199	10.5	10	15.75	0.957	7.9	100	Yes
NJ Pallet		70		48	40	72	80	553		No
NV Pallet		56		48	40	72	80	442.4		No