

47605-ACS



UPC Code: 07847709384

Country of Origin: Mexico - *Eligible for
ARRA funded projects > \$7,443,000

NEMA: 5-15R



Power and Surge Protection

Brand Features

Leviton offers reliable surge protective AC Power Modules and J-Box kits. Both the AC Power Module and the J-Box kits work with the Series 140, 280 and 420 Structured Media Centers. Choose either surge protective for optimum protection or non-surge protective. The surge protected options provide EMI/RFI filtering that meets UL 1449 standards. The AC Power Modules feature two 15-Amp duplex receptacles and the J-Box kit features one 15-Amp duplex receptacle.

Item Description

J-Box Surge Protective Kit (one duplex blue receptacle)

Technical Information

Electrical Ratings

Type: AC Power Module
Output Voltage: 120 Volt
Input Voltage: 120 Volt AC
Output Power: 15 Amp
NEMA: 5-15R

Product Features

Type: AC Power Module
Output Voltage: 120 Volt
Input Voltage: 120 Volt AC
Output Power: 15 Amp
Feature: Surge
NEMA: 5-15R

Material Specifications

Enclosure Material: Powder-Coated Steel

Quantity of Outlets: 2

Series Compatibility: 140, 280, 420 Series Compatible

Mechanical Specifications

Quantity of Outlets: 2

Standards and Certifications: UL

Warranty: 2 Year Limited

Performance Data

MCOV: 150V rms
Joules at 10/1000 micro-sec: 720
Max Surge Current L-N: 24kA
Noise Rejection: -30dB at 500kHz-30MHz
UL1449 Impulse 6kV/500A L-G: 400V
Diagnostics: Indicator Light & Audible Alarm

Standards and Certifications

NEMA: WD-6
ANSI: C-73
UL498HG: File E13399
UL1449 Std. 2nd Edition: File E146315
CSA C22.2 No. 42: File 152105
NOM: 057

Features and Benefits

- Hospital Grade surge-protected units provide greater protection for line-voltage modules, including multi-stage defense L-N,L-G,N-G.
- Provides 2 Outlets of protected power.
- Safety Clips protect outlets against dust, dirt and debris.
- Cable knockout on bottom for power service connection.
- Saves valuable real estate by mounting on outside of Structured Media Enclosures.
- Features EMI/RFI filtering and meets UL1449 standards.

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.
201 North Service Road, Melville, NY 11747
Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

Leviton Manufacturing of Canada, Ltd.
165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 ·
FAX: 1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.
Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com
© 2012-2014 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.



Leviton has a global presence.
If you would like to know where your local Leviton office is located please go to: www.leviton.com/international/contacts/

**Buy American Compliant Logo -- The American Recovery And Reinvestment Act of 2009 ("ARRA") provides federal grants and loans for projects throughout the country. Section 1605 of the Act, named the "Buy American" provision, requires that certain materials and manufactured products used in projects funded by the Act be manufactured in the United States. The appearance of the Recovery Act Logo in relation to a Leviton product is only intended to reflect that such product may be used in an ARRA funded project. It does not mean that such product or Leviton is sponsored or endorsed by, or that Leviton receives funds from, the federal government or the Recovery Accountability and Transparency Board. Nothing in Leviton's use of the logo is intended to suggest anything regarding the requirements for funding under ARRA.*