

Communication Technologies

Products

Solutions by Network

Documents & Resources

Support

Where to Buy

Contact Us

[United States](#) > [Electronics](#) > [Communication Technologies](#) > [Communication Technologies Product Catalog](#) > [Tapes](#) > [Vinyl Tapes](#) > 3M™ Temflex™ General Use Vinyl Electrical Tape 1700C, Green, 3/4 in x 66 ft (19 mm x 20,1 m), 100 per case

3M™ Temflex™ General Use Vinyl Electrical Tape 1700C, Green, 3/4 in x 66 ft (19 mm x 20,1 m), 100 per case

3M ID 80610736912 UPC# 00054007506515 Part Number 1700C-GREEN

• [Print](#)



The economical solution for less demanding indoor jobs. On a 1 1/2 inch core, this green, 7 mil vinyl tape serves as a general purpose tape. Inner pack of 1 per shrink wrap, 10 per sleeve with 100 rolls per case.

This tape is used for protective jacketing and harnessing. Flame retardant and cold resistant. UL Listed and CSA Certified for 176(deg)F (80(deg)C).

Need Help? [Contact Us](#) or [Call 1-800-3M](#)

Questions? We can help
[Contact Us](#)



Overview	Documents														
Specifications <table><tr><td>Brand</td><td>Temflex™</td></tr><tr><td>Color</td><td>Green</td></tr><tr><td>Length</td><td>66 Linear Foot</td></tr><tr><td>RoHS 2011/65/EU Compliant</td><td>Yes</td></tr><tr><td>RoHS EU Comments</td><td>RoHS 2011/65/EU compliant without exemption *Important RoHS information</td></tr><tr><td>Thickness</td><td>7 mil</td></tr><tr><td>Width</td><td>0.75 Inch</td></tr></table>		Brand	Temflex™	Color	Green	Length	66 Linear Foot	RoHS 2011/65/EU Compliant	Yes	RoHS EU Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information	Thickness	7 mil	Width	0.75 Inch
Brand	Temflex™														
Color	Green														
Length	66 Linear Foot														
RoHS 2011/65/EU Compliant	Yes														
RoHS EU Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information														
Thickness	7 mil														
Width	0.75 Inch														

3M Communication Technologies: [Connect to MyTelecom](#) | [Where to Buy](#) | [Contact Us](#) | [View Mobile Site](#)

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2017. All Rights Reserved.