

# 615CV



**Color:** Yellow

**UPC Code:** 07847784232

**Country Of Origin:** Mexico

*\*Eligible for ARRA funded projects > \$7,443,000*

**NEMA:**  
6-15R



# 615CV

## Brand Features

Leviton offers a large selection of 15, 20, 30 and 50 Amp Commercial Grade Straight Blade Plugs and Connectors, available in a wide variety of features. These rugged performers are moisture, chemical and abuse-resistant, And they're ideal for indoor and outdoor use. Our EPTR rubber-backed plugs and connectors stand up to rough use, protecting against dirt and moisture. The deep-slotted, backed-out terminal screws draw backwire clamps securely over stripped leads for maximum conductivity.

## Item Description

15 Amp-250 Volt,Nema 6-15R 2 Pole-3 Wire. Connector round dead front, yellow vinyl husk, face and clamps.

## Technical Information

### Electrical Specifications

**Dielectric Voltage:** Withstands 2000V per UL498

**Grounding:** Grounding

**Temperature Rise:** Max 30C after 50 cycles OL at 150 percent rated current

**Voltage:** 250 Volt

**Current Interrupting:** Certified for current interrupting at full rated current

**Amperage:** 15 Amp

**Wire:** 3

**Pole:** 2

### Environmental Specifications

**Operating Temperature:** -40C to 60C

**Flammability:** Rated V-2 per UL94

### Material Specifications

**Body Material:** PVC

**Color:** Yellow

**Blades/Contacts:** Brass

**Assembly Screws:** Steel, Zinc Plated

### Mechanical Specifications

**Product ID:** Ratings and NEMA I.D. permanently marked on device

**Terminal ID:** Brass-Hot, Green-Ground, Silver-Neutral

**Terminal Accom.:** 18-12 AWG

**Cord Range:** .245 - .700

### Product Features

**Color:** Yellow

**NEMA:** 6-15R

### Standards and Certifications

**Warranty:** 10-Year Limited

**CSA C22.2 No. 42:** File LR-406

**ANSI:** C-73

**UL498:** File E13393

**NOM:** 057

**NEMA:** WD-6

## SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

**Leviton Manufacturing Co., Inc.**

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

**Visit our Website at: [www.leviton.com](http://www.leviton.com)**

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)



*\*Leviton is the smart choice, providing the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial buildings. Leveraging more than a century of experience, Leviton helps customers create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, and lighting energy management systems. From switches and receptacles, to daylight harvesting controls, networking systems, and equipment for charging electric vehicles, Leviton solutions help customers achieve savings in energy, time and cost, all while enhancing safety.*