



Item #: **F900-BCW**  
 Product Family Name: **Cristafano™**  
 Category: **Interior Fan**  
 Certification: **E75795**  
 Patents: © 2005 Minka Lighting, Inc. test  
 Notes:

UPC Code: 706411029851  
 Finish: **Belcaro Walnut™**  
 Category Type: **Ceiling Fan**



Image File Name:  
 F900-BCW\_1.jpg



## MEASUREMENTS

Blade Finish:		Reversible Blades:	
		<b>No</b>	
Blade Material:		Slope:	
<b>Plywood Construction</b>		<b>No</b>	
Blade Sweep:	No. of Blades:	Blade Pitch:	Hanging Weight:
<b>68</b>	<b>5</b>	<b>14 degrees</b>	<b>41.89</b>
Downrod 1:	Downrod 1 Outside Dia:	Downrod 2:	Downrod 2 Outside Dia:
<b>3.5</b>	<b>.75</b>	<b>16</b>	<b>.75</b>
Ceiling to Lowest Point: (Dim A)	Ceiling to Blade: (Dim B)	Lead Wire:	Motor Size:
<b>14.00</b>	<b>13.00</b>	<b>80</b>	<b>212x25mm</b>

	Low:	Low/Med:	Medium:	Med/High:	High:
<b>RPM:</b>	<b>49</b>		<b>83</b>		<b>112</b>
<b>Amps:</b>	<b>0.47</b>		<b>0.70</b>		<b>0.83</b>
<b>Watts:</b>	<b>29.000</b>		<b>62.000</b>		<b>95.000</b>
<b>CFM:</b>	<b>2581.64</b>		<b>3810.99</b>		<b>6021.82</b>
<b>CFM/Watts</b>	<b>89.02</b>		<b>61.47</b>		<b>63.39</b>



## FAN CONTROLS

Pull Chain Control:	Works with Remote Control:	Works with Wall Control:
<b>No</b>	<b>Yes</b>	<b>Yes</b>
	Included Remote Control:	Included Wall Control:
		<b>WCS212</b>
	Compatible Remote Control[s]:	Compatible Wall Control[s]:
	<b>RCS212</b>	

## LAMPING

No. of Bulbs:	Light Type:			
<b>2</b>	<b>T4e11) Mini Cand Halogen Clear</b>			
Max Bulb Wattage:	Socket:			
<b>50</b>	<b>E11 Mini Cand</b>			
Light Kit:	Dimmable:	Ballast:	Rated Life Hours:	Uplight
<b>Yes</b>	<b>Yes</b>			<b>Y</b>
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
<b>Yes</b>				

## GLASS

Description:	Material:
Part No.:	Quantity:
<b>GF900</b>	<b>1</b>
Width:	Length:
Height:	



## SHIPPING

Carton Width:	Carton Height:	Carton Length:
<b>16.750</b>	<b>11.420</b>	<b>28.540</b>
Carton Weight:	Carton Cubit Feet:	Small Package Shippable:
<b>48.114</b>	<b>3.159</b>	<b>Yes</b>
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		<b>1</b>
		Master Pack:
		<b>1</b>



Title 17

Yes



UL Listed

Yes