



All 3M Products Newsroom About 3M

Search 

United States [Change]

Electrical Commercial and Industrial

[Products](#) | [Documentation & Literature](#) | [News & Tradeshows](#) | [Support](#)[United States](#) > [Energy](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Electrical Tape, Mastics & Special Use](#) > [Rubber Tapes - Insulating and Splicing](#) > [Scotch® Fire-Retardant Electric Arc Proofing Tape 77 Black, 3 in x 20 ft](#)[Find An Account Rep](#)[Where To Buy \(Find A Distributor\)](#)[Contact Us](#)

Scotch® Fire-Retardant Electric Arc Proofing Tape 77 Black, 3 in x 20 ft

3M ID 80611605983 UPC# 00051128603338 Part Number 77 Black-3x20FT

[Print](#)

Scotch® Fire-Retardant Electric Arc Proofing Tape 77 is designed to protect most types of electrical cables when exposed to potential failures in an adjacent cable. Its specially formulated adhesive expands in fire to form a thick char buildup between the flame and the cable. The resulting firewall acts as a heat shield and flame barrier, thus protecting the nearby cables and accessories.

- 3 in x 20 ft, Black
- Designed to protect most types of electrical cables when exposed to potential failures in an adjacent cable
- Specially formulated adhesive expands in fire to form a thick char buildup between the flame and the cable
- Firewall acts as a heat shield and flame barrier

Need Help?**Questions?** We can help
[Contact Us](#)**Overview****Documents**

The resulting firewall acts as a heat shield and flame barrier, thus protecting the nearby cables and accessories.

Specifications

Adhesive Material	Non-Adhesive
Backing Material	Intumescent elastomer
Brand	Scotch
Breaking Strength	36 lb/in
Color	Black
Elongation	150 %
Family	Scotch® Fire-Retardant and Electric Arc Proofing Tape 77/77W
Length	20 Linear Foot
Material	Non-Adhesive
RoHS 2011/65/EU Compliant	Undetermined
RoHS EU Comments	Contact 3M for information *Important RoHS information
Rolls per Carton	1
Rolls per Case	10
Self Sticking/Amalgamating	No
Specifications	Consolidated Edison Co. Test EO-5343-14
Tape Grade	Premium
Tape Type	Insulating and Splicing
Thickness	30 mil
UV Resistant	Yes
Width	3 Inch

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2017. All Rights Reserved.