


460B9W



Color:  Blue

UPC Code: 07847783759

460B9W

Item Description

60 Amp, 250 Volt 3-Phase, 3P, 4W, Inlet North American Pin & Sleeve Inlet, Industrial Grade, IP67, Watertight - BLUE

Technical Information

Electrical Specifications

Dielectric Voltage: 2000V for 1 min.

Voltage: 250 Volt 3-Phase

Current Interrupting: Certified for current interrupting at full rated current

Amperage: 60 Amp

Endurance: Up to 1000 connects and disconnects, under load, at full rated current and voltage

Wire: 4

Insulation Resistance: 500V for 1 min; $\geq 5M$

Pole: 3

Environmental Specifications

Corrosion Resistance: Ferrous parts immersed in 20°C, 10 percent ammonium chloride solution for 10 min

Moisture Resistance: Per UL 1682, immersed for 24 hours in 5cm of 25°C water

IP Rating: IP67, Watertight

Flammability: Rated V-0 per UL94

Material Specifications

Phase and Ground Pins: Brass

Body Material: Valox 357

Mounting Flange: Valox 357

Locking Ring: Valox 357

Contact Carrier: Reinforced Nylon

Terminal Screws: Steel

Gasket Material: Chloroprene

Product Features

IEC Rating: 60309-1 and 60309-2

Color: Blue

Standards and Certifications

UL Listed: 1682 and 1686


Warranty: 2-Year Limited

IEC Rating: 60309-1 and 60309-2


CE Marking: Per low voltage directives 73/23/EEC, 93/68/EEC

CSA Certified: C22.2 No 182.1

Dimensional Diagram



UNIT	A	B
inch	3.15	1.97
mm	80	50



SPECIFICATION SUBMITTAL

JOB NAME:		CATALOG NUMBERS:	
<input type="text"/>		<input type="text"/>	
JOB NUMBER:	<input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

