




Color:  Light Almond

UPC Code: 078477561959

Country Of Origin: China

6674-P0T

Universal Decora Dimmable LED, CFL and Incandescent SureSlide Slide Dimmer, 600W-120VAC Incandescent, and 150W-120VAC Dimmable LED and CFL, 60Hz, single pole and 3-way - Light Almond

Leviton Decora SureSlide® dimmers provide smooth, slide-action, full-range dimming for incandescent and dimmable LED and CFL lamps. Featuring a pre-set ON/OFF switch, this device allows the user to set the desired brightness level to operate automatically with the ON/OFF function. The dimmer is designed specifically for dimmable light-emitting diodes (LED) and dimmable compact fluorescent (CFL) lamps; it is also compatible for use with incandescent lamps.

Technical Information

Product Features

Action: Standard ON/OFF

Available Colors: Ivry-I Wht- W Blk-E Brwn-B Light Almond-T

California Title 24: Yes

Color: Light Almond

Frequency: 60 Hz

Light: None

Load Rating: 600W Incandescent, 150W LED and CFL

Load Type: Incandescent, Dimmable LED, Dimmable CFL

NEMA SSL 7A: Yes

Ordering Notes: Includes Ivory, White and Light Almond Color Kits

Preset: Preset

Protection: Radio/TV Filter

Standards and Certifications: UL/CSA

Style Name: SureSlide

Switch Type: Single-Pole & 3-Way

Type: Electro-Mechanical

Voltage: 120 VAC

Wallplate: Order Separately

Warranty: 5-Year Limited

Features and Benefits

- New updated look.
- Integrated linear full-range slide control for easy, precise operation.
- Features a separate ON/OFF switch that preserves the selected brightness setting.
- Single pole or 3-way lighting control when used with a 3-way switch.
- Slim, compact housing fits easily into a standard wallbox and is suitable for multi-gang installations.
- Future-proof to control a variety of dimmable CFL and LED lamps.
- Backwards compatible with incandescent lamps.
- Built-in radio/TV interference filter.
- Can be used to comply with 2016 California Title 24, Part 6 Indoor Lighting Switching Devices and Controls
- Available colors: White, Ivory, Light Almond, Black and Brown.

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):
+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

