

13654-TNP



UPC Code : 078477164891

Country Of Origin : Mexico

Miniature Base, T5 Bi-Pin, Standard Fluorescent Lampholder, Tall Profile, Snap-In or Slide-ON, Lamp-Lock, , Quickwire 18AWG Solid or Str Tinned - White

Technical Information

Mechanical Specifications

Contact Type : Lamp-Lock

Mounting Type : Snap-In or Slide-ON

Panel Thickness : 22-25 Ga. Panel

Rated Wattage : 120W

Termination : Quickwire 18AWG Solid or Str. Tinned

Voltage : 600 Volt

Wire Strip Length : 3/8 Inch

Product Features

Availability : OEM Only

Body Material : Thermoplastic

Color : White

Contact Material : Copper-Alloy

Contact Type : Lamp-Lock

Lamp Base : Miniature

Lamp Contacts : Bi-Pin

Lamp Type : T5

Lampholder Type : Linear

Light Type : Fluorescent

Mounting Type : Snap-In or Slide-ON

Panel Thickness : 22-25 Ga. Panel

Rated Wattage : 120W

Standards and Certifications :
UL/CSA/NOM

Style Name : Tall Profile

Termination : Quickwire 18AWG Solid or Str. Tinned

Warranty : 1 Year Limited

Standards and Certifications

CSA Certified : File LR-1863

NOM Certified : 057

UL Listed : File E5833

SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
JOB NUMBER:		

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):

+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

