


EI700 EI700R EI700AT EI700RAT EI700NB EI700ATNB

ERT713L - Black Metal Baffle

- Provides deeper lamp regression for BR lamps
- ERT713LTS - Torsion spring retention
- ET713L - Friction clip retention
- Lamps:




ERT713LTS
High Gloss Appliance White Trim with Black Baffle and Torsion Spring Construction

ERT713L
High Gloss Appliance White Trim with Black Baffle

EI700 EI700R EI700AT EI700RAT EI700NB EI700ATNB	75W BR40, 65W BR30, 75W PAR30L
--	--------------------------------------

ERT714 - Plastic Baffle

- Coil spring retention
- Lamps:




ERT714WHT
High Gloss Appliance White Trim with White Baffle

ERT714
High Gloss Appliance White Trim with Black Baffle

EI700 EI700R EI700AT EI700RAT	50W PAR30, 65W BR30, 75W PAR30L
--	---------------------------------

ERT704 Eyeball

- Torsion springs pull trim tight to ceiling
- Lamps:




ERT704PB
Polished Brass Trim with Polished Brass Eyeball

ERT704
High Gloss Appliance White Trim with White Eyeball

EI700 EI700AT EI700R EI700RAT EI700NB EI700ATNB	65W BR30, 75W R30, 75W PAR30L
--	----------------------------------

ERT711 Regressed Eyeball

- Lamps:




ERT711
High Gloss Appliance White Trim and Eyeball with Black Baffle

EI700 EI700AT EI700NB EI700ATNB	50W PAR30 65W BR30, 75W R30
--	--------------------------------

ERT705 - Open

- Coil Spring retention
- Lamps:




ERT705
High Gloss Appliance White Trim

EI700 EI700AT EI700R EI700RAT EI700NB EI700ATNB	65 W R30, 75W PAR30, 75W PAR30L
--	------------------------------------

ERT721 - Shower Light with Frosted Glass Lens and Reflector

- Torsion springs pull trim tight to ceiling
- Wet location listed for use in showers
- Lamps:



ERT721
High Gloss Appliance White Trim with Frosted Lens


EI700 EI700AT EI700R EI700RAT EI700NB EI700ATNB	40W A19
--	---------

ET700

ET700R

ERT721 - Shower Light with Frosted Glass Lens and Reflector

- Torsion springs pull trim tight to ceiling
- Full cone socket Supporting reflector
- Wet location listed for use in showers
- Lamps:




ERT721
High Gloss Appliance White Trim with Frosted Lens

ET700 ET700R	60W A19
-------------------------------	---------

ERT725 - Black Metal Baffle/Splay

- Combination baffle/splay trim
- Socket Supporting trim
- ERT725TS - Torsion spring retention
- ERT725 - Friction clip retention
- Lamps:




ERT725TS
High Gloss Appliance White Trim with Black Baffle and Torsion Spring Construction

ERT725
High Gloss Appliance White Trim with Black Baffle

ET700 ET700R	50W PAR30L, 85W BR30, 90W A19, 100W R30,
-------------------------------	--

ERT725WHT - White Metal Baffle/Splay

- Combination baffle/splay trim
- Socket Supporting trim
- ERT725WHTTS - Torsion spring retention
- ERT725WHT - Friction clip retention
- Lamps:




ERT725WHTTS
High Gloss Appliance White Trim with White Baffle and Torsion Spring Construction

ERT725WHT
High Gloss Appliance White Trim with White Baffle

ET700 ET700R	50W PAR30L, 75W PAR30L, 85W BR30, 90W A19, 100W R30,
-------------------------------	--

ERT723 - Shower Light with Glass Fresnel Lens and Reflector

- Torsion springs pull trim tight to ceiling
- Wet location listed for use in showers
- Socket supporting trim
- Lamps:



ERT723
High Gloss Appliance White Trim with Glass Fresnel Lens

ET700 ET700R	60W A19
-------------------------------	---------

* When using an Air-Tite trim to meet California Title 24 air tight compliance, an additional gasket is required between the finished ceiling and the trim flange ring. For California Title 24 compliance use accessory trim gasket GA-ATRIM. Order separately in a 6 pack: GA-ATTRIM-6PK

EI700U


EI700UAT

ERT705 - Open

- Coil Spring retention
- Lamps:

EI700U	75W PAR30, 75W
EI700UAT	PAR30L, 85W BR30, 100W R30

Aperture:
3-7/8" [98mm]
OD:
8" [203mm]



ERT705
High Gloss Appliance White Trim


ERT701

Albalite Lens Shower Light

- Wet Location listed for use in showers
- Torsion Spring retention
- Lamps:

EI700U	40W A19
EI700UAT	

OD:
8" [203mm]



ERT701
High Gloss Appliance White Trim with Albalite Lens


ERT702

Drop Opal Plastic lens Shower Light

- Wet Location listed for use in showers
- Torsion spring retention
- Lamps:

EI700U	40W A19
EI700UAT	

OD:
8" [203mm]



ERT702
High Gloss Appliance White Trim with Drop Opal Lens


ERT703

Fresnel Lens Shower Light

- Wet Location listed for use in showers
- Torsion spring retention
- Lamps:

EI700U	40W A19
EI700UAT	

OD:
8" [203mm]



ERT703
High Gloss Appliance White Trim with Glass Fresnel Lens


ERT721

Shower Light with Frosted Glass Lens and Reflector

- Wet Location listed for use in showers
- Torsion spring retention
- Lamps:

EI700U	60W A19
EI700UAT	

Height:
4-1/4" [108mm]H
OD:
8" [203mm]



ERT721
High Gloss Appliance White Trim with Frosted Diffuser


ERT708

Large Aperture Open

- Coil Spring Retention
- Lamps:

ET700	100W R40 (Requires
ET700R	H1999 Socket Extender)

Aperture:
5-3/16" [131mm]
OD:
8" [203mm]



ERT708
High Gloss Appliance White Trim

* When using an Air-Tite trim to meet California Title 24 air tight compliance, an additional gasket is required between the finished ceiling and the trim flange ring. For California Title 24 compliance use accessory trim gasket GA-ATRIM. Order separately in a 6 pack: GA-ATRIM-6PK

ALL-PRO™

EI2700


EI2700AT

EI2700R

ERT716 - Shallow Metal Baffle

- Socket Supporting trim
- Friction clip retention
- Lamps:

EI2700	65W BR30, 75W PAR30,
EI2700AT	75W PAR30L
EI2700R	75W PAR30L




ERT716
High Gloss Appliance White Trim with White Baffle

ERT704 - Eyeball

- Torsion springs pull trim tight to ceiling
- Lamps:

EI2700	65W BR30, 75W R30,
EI2700AT	75W PAR30L
EI2700R	65W BR30, 75W R30,
	75W PAR30L




ERT704PB
Polished Brass Trim with Polished Brass Eyeball

ERT704
High Gloss Appliance White Trim with White Eyeball

ERT711 - Regressed Eyeball

- Friction clip retention
- Lamps:

EI2700	50W PAR30
EI2700AT	
EI2700R	




ERT711
High Gloss Appliance White Trim and Eyeball with Black Baffle

ERT705 - Open

- Coil Spring retention
- Socket supporting trim
- Lamps:

EI2700	50W PAR30L, 60W
EI2700AT	BR30, 75W PAR30
EI2700R	60W BR30




ERT705
High Gloss Appliance White Trim

ERT721 - Shower Light, Frosted Glass Lens and Reflector

- Torsion springs pull trim tight to ceiling
- Socket supporting trim
- Wet location listed for use in showers
- Lamps:

EI2700	35W PAR30L
EI2700AT	
EI2700R	40W A19




ERT721
High Gloss Appliance White Trim with Frosted Lens

ERT723 - Shower Light with Glass Fresnel Lens and Reflector

- Torsion springs pull trim tight to ceiling
- Wet location listed for use in showers
- Socket supporting trim
- Lamps:

EI2700	35W PAR30L
EI2700AT	
EI2700R	40W A19



ERT723
High Gloss Appliance White Trim with Glass Fresnel Lens

* When using an Air-Tite trim to meet California Title 24 air tight compliance, an additional gasket is required between the finished ceiling and the trim flange ring. For California Title 24 compliance use accessory trim gasket GA-ATRIM. Order separately in a 6 pack: GA-ATTRIM-6PK

ET2700


ET2700R

ERT708

Large Aperture Open

- Coil spring retention
- Lamps:

ET2700	120W BR40, 150W R40
---------------	---------------------




ERT708
High Gloss Appliance White Trim

ERT701

Albalite Lens Shower Light

- Wet Location listed for use in showers
- Lamps:

ET2700	60W A19
---------------	---------




ERT701
High Gloss Appliance White Trim with Albalite Lens*

ERT702

Drop Opal Plastic Lens Shower Light

- Wet Location listed for use in showers
- Torsion spring retention
- Lamps:

ET2700	60W A19
---------------	---------




ERT702
High Gloss Appliance White Trim with Drop opal Lens

ERT703

Fresnel Lens Shower Light

- Wet Location listed for use in showers
- Torsion spring retention
- Lamps:

ET2700	60W A19
---------------	---------




ERT703
High Gloss Appliance White Trim with Glass Fresnel lens

ERT721

Shower Light with Frosted Glass Lens and Reflector

- Wet Location listed for use in showers
- Torsion spring retention
- Lamps:

ET2700R	60W A19
----------------	---------




ERT721
High Gloss Appliance White Trim with frosted diffuser

ERT723 - Shower Light with Glass Fresnel Lens and Reflector

- Torsion springs pull trim tight to ceiling
- Wet location listed for use in showers
- Socket supporting trim
- Lamps:

ET2700R	60W A19
----------------	---------



ERT723
High Gloss Appliance White Trim with Glass Fresnel Lens

* When using an Air-Tite trim to meet California Title 24 air tight compliance, an additional gasket is required between the finished ceiling and the trim flange ring. For California Title 24 compliance use accessory trim gasket GA-ATRIM. Order separately in a 6 pack: GA-ATTRIM-6PK