



# Ocal®

## Conduit Fittings-PVC Coated T&B Catalog Number:

**UPC Number:** CPL4-G  
70450836274  
**Status:** Active  
**Description:**

PVC Coated Conduit Coupling, 4 Inch/103 Metric Coupling Size, 3.19 Inch/80.97 Millimeters Minimum Length of Metal, 7.19 Inch/182.57 Millimeters Total Minimum Length Including Sleeve, Straight Threads, Pressure Sealing Sleeves, Blue Urethane Coating on Interior and Threads, Galvanized Rigid Steel, Gray

### Features

	Nominal .002 in. (2 mil) blue urethane coating on interior and exterior
	Minimum .040 in. (40 mil) PVC coating is bonded to the exterior
	Straight threads (NPS)
	Molded ribs on outer coating for easy installation, up to and including 4 in.
	Pressure sealing sleeves protect your connection

### General

Trade Size (inches)	4
Material	Steel
Finish	PVC Coated
Color	Dark Gray

### Dimension Information

Pipe Size (inches)	4
Pipe Size (Metric Size Designator*)	103

### Technical Information

Chemical Resistance Chart	Available on Website
---------------------------	----------------------

### Specifications

Ocal Specification Guide-1995 Master Format-PDF	Available on Website
Ocal Specification Guide-1995 Master Format-DOC	Available on Website
Ocal Specification Guide-2004 Master Format-PDF	Available on Website
Ocal Specification Guide-2004 Master Format-DOC	Available on Website

### Packaging

Package in Units	11
T&B Sold in UOM	Each
T&B Weight Per UOM	3.82 lbs. Each

### Application Support

T&B Sales Drawings	wsd-000545
Ocal Specifications	Available on Website

Recommended Installation Procedures	Available on Website
Product Overview-Conduit Outlet Bodies	Available on Website
NEMA Standards-RN 1	Available on Website
NEC 310-16 - Conductors for General Wiring	Available on Website
NEC Table 8	Available on Website

## Notes

Metric size designator (ANSI C80. 1-1994)

## Certifications

RoHS Compliance	Yes
-----------------	-----

## Certifications



File Nbr:  
E 46453

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com