

DESCRIPTION

A lampholder designed for use with Halo Power-Trac that utilizes standard PAR and halogen PAR lamp technology. Front loading of the lamp allows ease of relamping. Available in white or black finish. For use with Halo and Lazer-by-Halo track systems.

Well suited for accent lighting in commercial spaces, loft apartments, home offices and home theaters.

Catalog #	Type
Project	
Comments	
Prepared by	Date

SPECIFICATION FEATURES

A---Quick Lock Adapter

Polycarbonate casing. Attaches electrically and mechanically anywhere along Power-Trac. Visual polarity line assures proper grounding. Two position conductor allows use in single circuit and either circuit of two circuit track.

B---Arm

Yoke allows lampholder to rotate 338° horizontally and

provides 0° to 90° vertical pivot for maximum aiming adjustability.

C---Lampholder Body

Formed metal housing provides light weight and optimal heat dissipation. Available in three finishes—Satin White, Matte Black and Satin Metallic Silver.

D---Adjustment Knob

Large easy-to-use adjustment knob locks in aiming angles.


Labels

UL listed and CSA certified for use with Halo and Lazer-by-Halo track and track systems.



L1838


PAR LAMP  
STUDIO  
LAMP HOLDERS  
Power-Trac



ORDERING INFORMATION

SAMPLE NUMBER: L1838P

Lampholders	Finishes	Accessories
<div>L1838</div>	<div>P=Satin White MB=Satin Black SL=Satin Metallic Silver</div>	<div>See below</div>



L1838

For use with: 250W PAR38

W=5 7/8" [150mm]

L =7" [178mm]

E =10 3/4" [273mm]

Y =6" [154mm]

Accessories


L1977MB Barn Door Shutters - accepts 6 5/16" L300 Series Lenses and L277 Louver

L352MB Media Holder accepts 4 11/16" L200 Series Lenses and L275 Louver


## ACCESSORIES

**L352 Media Holder**

For use with L1838  
Lampholder to hold L200  
Series color filters and L275  
louver.



**L352 Media Holder****L1977MB Barn Door Shutters**

For use with L1838  
Lampholders to hold L300 color  
filters and L277 louver.

**L1977MB  
Barn Doors****L200 Series Color Filters**



Glass Filters 4 1 1/16" (119mm)  
diameter. For use with L1838  
with L352MB Media Holder.

L211=Medium Pink Color Filter  
L212=Warm Red Color Filter  
L214=Ultraviolet Filter  
L220=Daylight Blue Color Filter  
L221=Medium Blue Color Filter  
L231=Medium Amber Color Filter  
L241=Medium Green Color Filter

**L200 Color Filters****L300 Series Color Filters**

Glass Filters 6 5/16" (160mm)  
diameter. For use with L1838  
and L1977MB Barn Door.


L312=Warm Red Color Filter  
L314=Ultraviolet Filter  
L320=Daylight Blue Color Filter  
L330=Straw Color Filter  
L331=Medium Amber Color Filter  
L341=Medium Green Color Filter

**L300 Color Filters****L275 Cube Cell Louver**

4 3/4" OD (121mm). Black finish  
1/2" cells for directing light and  
eliminating glare. For use with  
L1838 and L352MB Media Holder.

**L277 Cube Cell Louver**

6 1/4" OD (159mm). Black finish  
1/2" cells for directing light and  
eliminating glare. For use with  
L1838 and L1977MB Barn Doors.

**Cube Louvers**

Note: Specifications and Dimensions subject to change without notice.

Visit our web site at [www.cooperlighting.com](http://www.cooperlighting.com)