SSLAIS LBR LED Lamp



Solais LED LBR Lamp Replacement



Product Description: Solais Lighting's newest family of LED lamps offers a unique replacement solution for traditional lighting sources – providing the incandescent performance, light output and aesthetics with our recessed OPTICS² patent-pending technology.

Performance Summary: Fully dimmable / BR form factor (ANSI-compliant) / Lightest LED lamps on the market / Certified to UL Standard 1993 / RoHS-compliant / Contain no lead or mercury

Applications: Designed for use in track and recessed fixtures.

OPTICS² Technology: Optics Squared technology is a patent-pending system in Solais LED passive lamps that incorporates a primary recessed and secondary surface dual-optic process, which allows Solais to duplicate the performance and aesthetics of incandescent light sources.

LBR40 / FL / 27K Form Factor Beam Angle CCT BR40 Food 2700K											
Product Code	Power (Watts)	Beam Angle	ССТ (К)	Lumen Output	CRI	Power Factor	Base Type	Weight (oz.)	Length (in.)	Diam. (in.)	Dim.
LBR40											
LBR40/FL/30K	16	Flood	3000	950	85	.92	E26	7.7	6.4	4.9	Yes
LBR40/FL/27K	16	Flood	2700	900	85	.92	E26	7.7	6.4	4.9	Yes
LBR30											
LBR30/FL/30K	14	Flood	3000	850	85	.92	E26	6.6	5.4	3.9	Yes
LBR30/FL/27K	14	Flood	2700	800	85	.92	E26	6.6	5.4	3.9	Yes

5-Year Warranty: Lamps are designed for an L70 of 50,000 hours. For directional lamps, ENERGY STAR® early submission dictates that manufacturers can claim only a 25,000-hour life, with 3,000-hour actual life test data, 6,000-hour LM-80 data and in-situ temperature measurements. Refer to the ENERGY STAR website for additional information.

LIMITED WARRANTY: Turolight warrants that this lamp will operate for a period of five (5) years from the date of purchase when used in accordance with package and lamp directions. If this lamp does not last for three years, return this product to the place of purchase or visit turolight.com for warranty replacement procedures. You must include the original receipt/ proof of purchase. Turolight will repair or replace your lamp. This limited warranty may not cover lamps subject to misuse, electrical current fluctuation, accident, neglect, or acts of God. THIS REPLACEMENT IS THE SOLE WARRANTY OBLIGATION OF TUROLIGHT AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLED, INCLIDING ANY WARRANTY OF MECHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. LIABILITY FOR INCIDENTAL AND CONSEQUENTIAL DAMAGES ARE EXCLUDED. Exclusion of incidental or consequential damages is not allowed by some provinces, so the above limitation or exclusion may not apply to you. Please visit turolight.com and contact us using the form supplied with any questions. **WARNING:** Not for use in fully enclosed luminaires. **Caution:** Risk of electric shock. Use in an indoor, dry location only. This device is not intended for use with emergency exit fixtures or emergency exit lights. May not be compatible with all dimmers, please contact Turolight.com for up-to-date dimmer compatibility information. **NOTES:** This product may cause interference with other devices. If interference occurs, change the location of the products involved.