

# MAX PUNCH® PRO KNOCKOUT TOOL

Heavy duty knockout punch driver for mild and stainless steel

## REMOVABLE DRAWSTUDS

Universal to fit most common KO dies

## NO HYDRAULICS, NO RATCHETING, NO MESS

An advanced knockout tool used with a cordless drill to draw punch dies together for quick accurate knockouts

## HEAVY DUTY

Cuts through 10 gauge stainless steel up to 4 inches



[southwiretools.com](http://southwiretools.com)

BUILT FOR DURABILITY. BUILT FOR RELIABILITY.  
**BUILT FOR WORK.**



**Southwire™**

## FEATURES & BENEFITS

### HEAVY DUTY KNOCKOUT PUNCH DRIVER FOR MILD AND STAINLESS STEEL.

- An advanced knockout tool used with a cordless drill to draw punch dies together for quick accurate knockouts
- No hydraulics, no ratcheting, no mess
- Thread-in / thread-out removable drawstuds (universal to fit most common KO dies)
- Rated to cut 10 gauge mild and stainless steel up to 4"
- Minimum drill recommendations: 18v cordless, equivalent of 550 in. lbs. torque rated

## SPECIFICATIONS

MODEL #	STOCK#		LENGTH	WIDTH	DEPTH	HEIGHT / WEIGHT	DESCRIPTION
MP-01PRO	57177501	UNBOXED	11.5"	5"	4.25"	5.5"	MAX PUNCH® PRO: drive unit only (no case)
MP-01CSPRO	57177601		16.5"	13"	11"	37 LBS	MAX PUNCH® PRO STAINLESS STEEL 1/2" - 4" SET
MP-01SDPRO	57177701		16.5"	13"	8.5"	14.5 LBS	MAX PUNCH® PRO STAINLESS STEEL 1/2" - 2" SET
MP-01CS	56830801		16.5"	13"	11"	37 LBS	MAX PUNCH® MILD STEEL 1/2" - 4" SET
MP-01SD	56830901		16.5"	13"	8.5"	14.5 LBS	MAX PUNCH® MILD STEEL 1/2" - 2" SET

### MAX PUNCH® PRO STAINLESS STEEL SETS

- MP-01CSPRO Includes:
  - Max Punch PRO drive unit
  - 1/2" - 4" Cutting dies (rated for stainless steel)
  - 2 Drawstuds sizes 3/4" & 7/16"
  - Maxis® Marksman® conduit layout tool
  - Step drill bit (3/16" - 7/8", 2 nut drivers) (3/8")
  - 2 Heavy duty carrying cases
- MP-01SDPRO Includes:
  - Max Punch PRO drive unit
  - 1/2" - 2" Max Punch PRO cutting dies (rated for stainless steel)
  - 2 Drawstuds sizes 3/4" & 7/16"
  - Maxis® Marksman® conduit layout tool
  - Step drill bit (3/16" - 7/8", 2 nut drivers) (3/8")
  - Heavy duty carrying case



### MAX PUNCH® PRO MILD STEEL SETS

- MP-01CS Includes:
  - Max Punch PRO drive unit
  - 1/2" - 4" Cutting dies (rated for mild steel)
  - 2 drawstuds sizes 3/4" & 7/16"
  - Maxis® Marksman® conduit layout tool
  - Step drill bit (3/16" - 7/8" 2 nut drivers) (3/8")
  - 2 Heavy duty carrying cases
- MP-01SD Includes:
  - Max Punch PRO drive unit
  - 1/2" - 2" Max Punch PRO cutting dies (rated for mild steel)
  - 2 Drawstuds sizes 3/4" & 7/16"
  - Maxis® Marksman® conduit layout tool
  - Step drill bit (3/16" - 7/8" 2 nut drivers) (3/8")
  - Heavy duty carrying case



Southwire Company  
One Southwire Drive  
Carrollton, GA 30119



Southwire™



Customer Service: 1-855-SWTOOLS (855-798-6657)

Scan code to see more  
Southwire Tools

[southwiretools.com](http://southwiretools.com)