

Ocal[®]

Conduit Bodies & Covers-PVC Coated T&B Catalog Number:



UPC Number: C17-G
Status: 70450835828
Description: Active

PVC Coated Conduit Body, C Shape, Form 7, Size 1/2 Inch/16 Metric, Iron, Dark Gray

Features

The conduit body and cover are double coated with a nominal .002 in. blue urethane on both the interior and exterior, before PVC coating is applied. A minimum of .040 in. PVC coating is bonded to the exterior.

Covers are coated with a molded flange to seal the conduit body while the conduit body is molded with a flat surface on its opening to seal with the cover.

Ocal pressure-sealing sleeves on all threaded hubs. Ocal conduit bodies are shipped with a cover and encapsulated stainless steel screws.

Bodies are designed with a flat back, allowing more cubic inch capacity. The flat back also keeps the body more stable during installation, requiring fewer conduit straps.

Application

- Act as pull outlets for conductors being installed
- Provide openings for making splices and taps in conductors
- Connect conduit sections
- Provide taps for branch conduit runs
- Make 90° bends in conduit runs
- Provide for access to conductors for maintenance and future system changes

General


Custom_Finish	f7c12
Trade Size (inches)	1/2
Material	Gray Iron
Finish	PVC Coated
Color	Dark Gray
Conduit Body Shape	C

Dimension Information

Dimension A (inches)	5.45
Dimension B (inches)	1.4
Dimension C (inches)	1.45
Dimension D (inches)	0.95
Dimension E (inches)	3.2

Technical Information

Chemical Resistance Chart	Available on Website
---------------------------	----------------------



Specifications

Ocal Specification Guide-1995 Master Format-PDF	Available on Website
Ocal Specification Guide-1995 Master Format-DOC	Available on Website
Ocal Specification Guide-2004 Master Format-PDF	Available on Website
Ocal Specification Guide-2004 Master Format-DOC	Available on Website

Packaging

Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	1.47 lbs. Each

Application Support

Ocal Specifications	Available on Website
Recommended Installation Procedures	Available on Website
Product Overview-Conduit Outlet Bodies	Available on Website
NEMA Standards-RN 1	Available on Website
NEC 310-16 - Conductors for General Wiring	Available on Website
NEC Table 8	Available on Website

Notes

Dimensional values are of uncoated conduit bodies.
Available in dark gray, white and light blue. Custom
colors are also available upon request. Please con-
tact Technical Services-888-862-3289

Certifications

File Nbr:
E 2969

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com