



Representative

**Catalog Number:** 1207AAY-001  
**Product ID:** 7TAA234010R0051  
**UPC Number:** 03448100246  
**Status:** A

ENT Flexible Raceway, Size 3/4 Inch, Nominal Inner Diameter 0.76 Inches, Nominal Outer Diameter 1.05 Inches, Minimum Bend Radius 6 Inches, Color Yellow, Length 1000 Feet

- One piece ENT coupling, threaded terminator and rigid non-metallic conduit fittings are rated concrete tight without tape.
- Lightweight, hand bendable, and free from sharp edges which reduces installation time and saves money.

#### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Carlton
Type	ENT Flexible Raceway
Special Features	Recognized for use with PVC rigid non-metallic conduit fittings with all size of ENT.
Application	Flex-Plus Blue ENT is a non-metallic flexible raceway for use in walls, floors, and non-plenum ceilings.
Standard	UL e73317
Trade Size	3/4 Inch
Outside Diameter	1.05 in
Inside Diameter	0.76 in
Length	1,000 ft
Material	Non-Metallic
Color	Yellow

#### European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	19.05mm
Nominal size in inch	3/4 inch
Outer diameter	26.67mm
Inner diameter	19.304mm
Material	PVC
Colour	Other
Sheathing material	Not sheathed
Approved according to DIN EN 61386-23	N
Approved according to UR	N
Approved according to LUL/British Standard	N
Approved according to Lloyd's Register TA	N
Approved according to UTAC	N
Approved according to DIN 5510	N
Approved according to NF F 16-101	N

#### Packaging

Outer Quantity	1000
Outer Dimensions (inches)	1x1x1
Weight Uom	0.15 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Support/Tools	Available on Website

**For further technical assistance, please contact us...**

ABB Installation Products - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

ABB Installation Products Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)