

# T5832-I

# Tamper Resistant Receptacles



**UPC Code:** 07847768393

**Country of Origin:** China

**NEMA:** 5-20R



## Brand Features

The Leviton USB Charger/Tamper-Resistant Duplex Receptacle offers two high-powered USB Ports with 3.6A of charging power and two 20A or 20A/125V Tamper-Resistant Receptacles. It has the capability to charge two USB powered electronic devices utilizing its two USB Ports, leaving the two Tamper-Resistant Receptacles free for other uses. The Leviton USB Charger/Tamper-Resistant Duplex Receptacle is designed to charge tablets, smart and mobile phones, gaming devices, e-readers, digital cameras and a host of other electronic devices.

## Item Description

Combination Duplex Receptacle/Outlet and USB Charger. 20 Amp, 125 Volt, Decora Tamper-Resistant Receptacle/Outlet, NEMA 5-20R. 3.6 Amps, 5VDC, 2.0 Type A USB Chargers. Grounding, Side Wired & Back Wired - Ivory.

## Technical Information

### Electrical Specifications

**Receptacle Amperage:** 20 Amp

**Amperage:** 20 Amp

**Receptacle Voltage:** 125V AC

**Ratings:** 20A-125V

**Horsepower Rating:** 20A-1 HP

**Grounding:** Grounding

### Mechanical Specifications

**Torque Range:** 12-14 inch pounds

**Terminal Accom.:** 14-12 AWG

**Product ID:** Stamped on Strap

**Termination:** Back & Side

**Terminal ID:** Brass-Hot Black-Hot White-Neutral Green-Gnd

### Environmental Specifications

**Operating Temperature:** -10C to 40C

**Flammability:** Rated V-0 per UL94

### Product Features

**Color:** Ivory

**Grade:** Residential

**NEMA:** 5-20R

### Material Specifications

**Cover Material:** Thermoplastic

**Strap Material:** Steel

**Color:** Brown

**Body Material:** Thermoplastic

### Standards and Certifications

**Warranty:** 5 Year Limited

**Listed:** cCSAus

**NOM:** 057

**FCC Part 15:** Class B for Residential Compliance

## Features and Benefits

- Perfect for use in residential applications such as kitchens, bedrooms and home offices and in commercial applications such as hotels, airports, restaurants and cafes, salons, office cubicles and college dorm rooms
- Smart chip recognizes and optimizes the charging requirements of individual devices
- USB Ports are positioned vertically providing more space for maneuvering and reducing stress on USB cables
- Compatible with USB 2.0 devices
- Fits in a standard wallbox, is compatible with standard wallplates and can be multi-ganged with other devices
- Easy to install. Can replace existing outlets

**SPECIFICATION SUBMITTAL**

<b>JOB NAME:</b> <input type="text"/>	<b>CATALOG NUMBERS:</b> <input type="text"/>	
<b>JOB NUMBER:</b> <input type="text"/>	<input type="text"/>	<input type="text"/>

**Leviton Manufacturing Co., Inc.**  
201 North Service Road, Melville, NY 11747  
Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**  
165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 ·  
FAX: 1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**  
Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

**Visit our Website at: [www.leviton.com](http://www.leviton.com)**  
© 2012-2016 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

**Leviton has a global presence.**  
If you would like to know where your local Leviton office is located please go to: [www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

