

# MINKA-LAVERY®

Item #: <b>4963-84</b>	UPC Code: <b>747396068411</b>
Product Family Name: <b>Overland Park</b>	Finish: <b>Overland Park</b>
Category: <b>Mini Chandeliers</b>	Category Type: <b>Mini Chandelier</b>
Certification <b>4000164</b>	
Patents	
Notes:	



Image File Name:  
4963-84--  
1378919622.jpg



## MEASUREMENTS

Width: <b>16</b>	Length: <b>16</b>	Height: <b>15.75</b>	Extension: <b></b>
Height Adjustable: <b>Yes</b>	Min Overall Height: <b>19.00</b>	Max Overall Height: <b>89.50</b>	Slope: <b>Yes</b>
Wire Length: <b>120</b>	Chain Length: <b>72</b>	Safety Cable Included: <b>No</b>	Net Weight: <b>8.51</b>
Canopy Width: <b>5.50</b>	Canopy Height: <b>0.75</b>	Canopy Length: <b></b>	
Backplate Width: <b></b>	Backplate Height: <b></b>	Center to Top: <b></b>	Center to Bottom: <b></b>

## LAMPING

No. of Bulbs: <b>3</b>	Light Type: <b>A-19,Medium</b>			
Max Bulb Wattage: <b>100</b>	Socket: <b>E26,Medium</b>			
Dimmable: <b>Yes</b>	Ballast: <b></b>	Rated Life Hours: <b></b>	Photocell Included: <b>N</b>	Lamps Included: <b>No</b>
Lamp Included: <b>No</b>	Color Temp.: <b></b>	CRI: <b></b>	Initial Lumens: <b></b>	Delivered Lumens: <b></b>

## SHADE / GLASS

Description: <b></b>	Material: <b>Glass</b>
Part No.: <b>G4961</b>	Quantity: <b>3</b>
Width: <b>4.75</b>	Height: <b>5.75</b>
	Length: <b>4.75</b>



## SHIPPING

Carton Width: <b>8.500</b>	Carton Height: <b>17.250</b>	Carton Length: <b>16.250</b>
Carton Weight: <b>11.660</b>	Carton Cubit Feet: <b>1.379</b>	Small Package Shippable: <b>Yes</b>
Master Pack Width: <b></b>	Master Pack Height: <b></b>	Master Pack Length: <b></b>
Master Pack Weight: <b></b>	Master Cubic Feet: <b></b>	Multi-Pack: <b>1</b>
		Master Pack: <b>1</b>



Damp  
Location  
**Yes**



ETL Intertek  
**Yes**