

2363



UPC Code: 07847780804

Country Of Origin: United States

\* Eligible for ARRA funded projects

NEMA:  
L10-20R



Made in USA



2363

#### Brand Features

Leviton's industry leading locking devices, such as our Black & White line of industrial grade plugs and connectors and receptacles, offer superior performance, long lasting reliability and other features that are backed by a lifetime warranty.

#### Item Description

20 Amp, 125/250 Volt, NEMA L10-20R, 3P, 3W, Locking Connector, Industrial Grade, Non-Grounding - BLACK-WHITE

#### Technical Information

##### AC Horsepower Ratings

**At Rated Voltage:** 2 HP L-L / 1 HP L-N

##### Electrical Specifications

**Dielectric Voltage:** Withstands 2000V per UL498

**Grounding:** Non-Grounding

**Temperature Rise:** Max 30C after 250 cycles OL at 200 percent rated current

**Voltage:** 125/250 Volt

**Current Interrupting:** Certified for current interrupting at full rated current

**Amperage:** 20 Amp

**Wire:** 3

**Pole:** 3

##### Environmental Specifications

**Operating Temperature:** -40C to 60C

**Flammability:** Rated HB or better UL94

##### Material Specifications

**Body Material:** Impact Modified Nylon

**Back Cover:** Thermoplastic

**Terminal Screws:** Brass

**Wire Module:** Nylon

**Color:** Black-White

**Cord-Clamp:** Nylon

**Blades/Contacts:** Solid Brass

**Clamp Insert:** Nylon

**Assembly Screws:** Steel, Zinc Plated

##### Mechanical Specifications

**Product ID:** Ratings are permanently marked on device

**Terminal ID:** Brass-Hot, Green-Ground, Silver-Neutral

**Terminal Accom.:** 18-10 AWG

**Cord Range:** .385 - .780

**Wire Gauge:** 16-10 AWG

##### Product Features

**Color:** Black-White

**NEMA:** L10-20R

##### Standards and Certifications

**Warranty:** Lifetime Warranty

**CSA C22.2 No. 42:** File LR-406

**UL Fed Spec WC-596:** File E13393


**ANSI:** C-73

**UL498:** File E13393


**NOM:** 057

**NEMA:** WD-6

### Dimensional Diagram



### Wiring Diagram



### SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

#### Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

#### Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

#### Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

Visit our Website at: [www.leviton.com](http://www.leviton.com)

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

#### Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)



*\*Leviton is the smart choice, providing the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial buildings. Leveraging more than a century of experience, Leviton helps customers create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, and lighting energy management systems. From switches and receptacles, to daylight harvesting controls, networking systems, and equipment for charging electric vehicles, Leviton solutions help customers achieve savings in energy, time and cost, all while enhancing safety.*