

12" Square Flush Mount

LED

54616142

14 Watt 1020lms Square Flush Mount Specifications




The ETi 14 watt 1020 lumen LED square flush mount fixture offers exceptional performance for precision lighting applications, while reducing energy and maintenance cost when compared with conventional light sources. Lasting over 10 times longer, these flush mount fixtures are high quality replacements for incandescent flush mount fixtures and is available in 4000K. They are UL listed for use in damp and dry locations. Warranty 5 years. Suitable for installations from - 4° F to 95° F.

KEY FEATURES & BENEFITS

- 14 Watts
- 120V
- 1020 lumen, 4000K CCT
- Dimmable
- UL damp location rated
- No UV, IR or mercury
- Warranty 5 years or 50,000 hours



FIXTURE DIMENSIONS



SKU# 54616142

Dimension A = 12.0"

Dimension B = 3.2"

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, please see www.etiled.us/fcc15b

APPLICATION INFORMATION

Designed to be used anywhere a standard incandescent fixture is used. Typically used in bedrooms, hallways, kitchens, living rooms and recreational rooms. Other applications apply in commercial, office, retail, restaurants, schools, hospitals and hotel/motel locations.



12" 14 Watt 1020lms Square Flush Mount

LED 54616142

SPECIFICATION DATA

Project _____

Item Number _____


Prepared by _____ Date _____

ORDERING INFORMATION

Item Number	Description	Wattage	Input Voltage (VAC)	Average Rated Life ¹	Typical Lumens ²	CCT ³	CRI ⁴	Power Factor	R9	Duv	CBCP	Beam	Operating Frequency
54616142	LED14w FLUSH-MOUNT 840120 DIM	14	120	50,000	1020	4000K	84.6	>.99	46	0.0004	279	120	60Hz
¹ Hours lifetime with 70% lumen maintenance													
² Thermally stable typical lumens (±10%)													
³ Thermally stable CCT (±10%)													
⁴ Color rendering index/Ra													

SHIPPING INFORMATION

Item Number	Item UPC	Item Dimensions (H x L x W)	Item Weight (lbs)	Inner Pack Qty	Inner Carton Bar Code	Inner Carton Dimensions (H x L x W)	Inner Pack Weight (lbs)	Master Pack Qty	Master Carton Bar Code	Master Dimensions (H x L x W)	Master Pack Weight (lbs)
54616142	836607009111	14" x 13.9" x 4"	2	N/A	N/A	N/A	N/A	4	50836607009116	16.9" x 15" x 14.5"	9.9



**The Americas Headquarters
720 Corporate Woods PKWY
Vernon Hills, IL 60061**

855-384-7754 www.etissl.com