



TKO™ Carbide Tipped Hole Cutters



Product Resources

Brochure

[TKO™ Carbide Tipped Hole Cutters Brochure](#)
(PDF - 1134KB)

[TKO™ Carbide Tipped Hole Cutters Brochure \(French\)](#)
(PDF - 502KB)

Features

- SmoothStart™ pilot drill prevents carbide damage by gradually guiding cutter to material
- Precision ground carbide teeth for fast cutting of clean, round holes
- Designed specifically for sheet metal cutting, even stainless steel
- Over drill flange built in to prevent penetration beyond the sheet metal

Models

Description	Hole Size (in.)	Conduit and Pipe Size (in.)	Cat. No.
TKO™ Carbide Tipped Hole Cutter, 3/4 in.	3/4	-	36-300
TKO™ Carbide Tipped Hole Cutter, 7/8 in.	7/8	1/2	36-301
TKO™ Carbide Tipped Hole Cutter, 1 in.	1	-	36-302
TKO™ Carbide Tipped Hole Cutter, 1-1/8 in.	1-1/8	3/4	36-303
TKO™ Carbide Tipped Hole Cutter, 1-1/4 in.	1-1/4	-	36-304
TKO™ Carbide Tipped Hole Cutter, 1-3/8 in.	1-3/8	1	36-305
TKO™ Carbide Tipped Hole Cutter, 1-7/16 in.	1-7/16	-	36-306
TKO™ Carbide Tipped Hole Cutter, 1-1/2 in.	1-1/2	-	36-307
TKO™ Carbide Tipped Hole Cutter, 1-3/4 in.	1-3/4	1-1/4	36-308
TKO™ Carbide Tipped Hole Cutter, 2 in.	2	1-1/2	36-309
TKO™ Carbide Tipped Hole Cutter, 2-1/2 in.	2-1/2	-	36-310
TKO™ Carbide Tipped Hole Cutter Kit; includes 4-Pieces - SmoothStart™ Replacement Tip, 7/8 in., 1-1/8 in. and 1-3/8 in. sizes	-	-	36-311
SmoothStart™ Replacement Pilot Drill	-	-	36-312
TKO™ Carbide Tipped Hole Cutter Kit; includes 8-Pieces - (2) SmoothStart™ Replacement Tips, 7/8 in., 1-1/8 in., 1-3/8 in., 1-3/4 in.,	-	-	36-314

2 in., and 2-1/2 in.			
----------------------	--	--	--

©2017 IDEAL INDUSTRIES, INC. All rights reserved.