

IPL06-10Z



UPC Code: 07847756186

Country Of Origin: China

IPL06-10Z

Brand Features

Leviton offers many products that will help lower electrical costs and add convenience to everyday living. By simply replacing standard switches with dimmers reduces energy consumption and extends bulb life. IllumaTech Preset Dimmers and Fan Speed Controls feature a low-profile fluid slide bar movement for fine adjustment of light levels or fan speeds that's accompanied by an easy-to-use ON/OFF preset switch. The switch provides quick ON/OFF control without disturbing your favorite pre-selected settings. Most feature a built-in LED locator light, as well. Models are available for incandescent, magnetic or electronic low-voltage, and Mark 10 Powerline dimming-ballast fluorescent lighting, and quiet and standard fan speed control.

Item Description

Universal Decora Dimmable LED, CFL and Incandescent IllumaTech Slide Dimmer, 600W-120VAC Incandescent, and 150W-120VAC Dimmable LED and CFL, 60Hz, single pole and 3-way. - White, Ivory & Light Almond

Technical Information

Product Features

Action: Standard ON/OFF

Warranty: 5-Year Limited

Preset: Preset

Color: White Ivory Light Almond

Switch Type: Single-Pole & 3-Way

Color Change Kit: IPKIT Series

Load Type: Incandescent, Dimmable LED, Dimmable CFL

Available Colors: Ivry-I Wht-W Gry-G Blk-E Brwn-B Light Almond-T, R-Red

Wallplate: Order Separately

Type: Electro-Mechanical

Load Rating: 600W Incandescent, 150W LED and CFL

Light: None

Voltage: 120 VAC

Style Name: IllumaTech

Ordering Notes: Incl White, Ivory and Light Almond Color Kit

Standards and Certifications: UL/CSA

Protection: Radio/TV Filter

Features and Benefits

- IPL06 designed specifically for dimmable LED and CFL lamps as well as incandescent
- Features a built-in starting technology for CFL lamps
- Wider dimming range on LED and CFL lamps than conventional incandescent dimmers
- Optional programming feature allows for users to modify the dimming range to optimize low light level performance when required
- Attractive styling coordinates perfectly with Leviton's complete line of Decora wiring devices
- Compatible with Decora Plus™ screwless and Decora standard designer wallplates
- Fit easily into a standard wallbox and are suitable for multi-gang installations
- IllumaTech controls come packaged with six product options in each box for superior versatility; 3 changeable color faces and single pole or 3-way control

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	<input type="text"/>
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

