

GFTR2-HGI



UPC Code: 07847772380

Country of Origin: China

NEMA: 5-20R



Tamper Resistant Receptacles

Item Description

20 Amp, 125 Volt, SmartlockPro Slim Self-Test GFCI Receptacle, Extra-Heavy Duty Hospital Grade, Tamper-Resistant, NEMA 5-20R, 20A Feed-Through, 2P, 3W, Matching Wallplate Included - IVORY

Technical Information

AC Horsepower Ratings

At Rated Voltage: 1 HP

Electrical Specifications

Grounding: Self-Grounding Clip

Pole: 2

Wire: 3

Short Circuit Current Rating: 10kA

Environmental Specifications

Flammability: Rated V-0 per UL94

Operating Temperature: -35C to +66C

Material Specifications

Face Material: PBT

Body Material: Polycarbonate

Terminal Screws: Plated Steel

Terminal Clamp: Brass

Line Contacts: Brass

Grounding Screw: Plated Steel

Strap Material: Galvanized Steel

Ground Clips: Brass

Shutter Mechanism: Delrin® Acetal

Mechanical Specifications

Terminal ID: Brass-Hot, Green-Ground, Silver-Neutral

Terminal Accom.: 14-10 AWG solid or stranded

Product ID: Ratings are permanently marked on device

Product Features

Color: Ivory

NEMA: 5-20R

Standards and Certifications

NEMA: WD-1 & WD-6



ANSI: C-73

Certification/Listing: UL, CSA, NOM-ANCE

Applicable Standards: UL 943, UL 498, CSA C22.2 No. 42 & 144, FedSpec W-C-596

Warranty

Product Warranty: 2-Year Limited



SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 ·

FAX: 1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012-2016 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to: www.leviton.com/international/contacts/

