

# T5361-CH



UPC Code: 07847770341

Country Of Origin: Mexico

\*Eligible for ARRA funded projects > \$7,443,000



# T5361-CH

## Item Description

20 Amp, 125 Volt, NEMA 5-20R, 2P, 3W, Single Receptacle, Tamper-Resistant, Straight Blade, Clock Hanger Receptacle, Stainless Steel Wallplate, Back & Side Wired - WHITE

## Technical Information

### AC Horsepower Ratings

**At Rated Voltage:** 1 HP

### Electrical Specifications

**Dielectric Voltage:** Withstands 2000V per UL498

**Temperature Rise:** Max 30C after 100 cycles OL at 150 percent rated current

**Voltage:** 125 Volt

**Amperage:** 20 Amp

**Wire:** 3

**Pole:** 2

### Environmental Specifications

**Operating Temperature:** -40°C to 75°C

**Flammability:** Rated V-2 per UL94

### Material Specifications

**Strap Material:** Zinc-Plated Steel

**Wallplate:** Stainless Steel

**Face Material:** Nylon

**Body Material:** Nylon

**Mounting Screws:** Steel

**Line Contacts:** Brass Triple-Wipe

**Grounding Screw:** Steel

### Mechanical Specifications

**Terminal ID:** Brass-Hot, Green-Ground, Silver-Neutral

**Termination:** Back & Side

**Terminal Accom.:** 14-10 AWG

### Product Features

**Device Type:** Single Receptacle

**Feature:** Tamper-Resistant

### Standards and Certifications

**Applicable Standards:** UL 498, UL514A, CSA C22.2 No. 42, CSA C22.2 No 18.1-04


**Certification/Listing:** cCSAus, NOM-ANCE

**ANSI:** C-73

**NEMA:** WD-1 & WD-6

### Warranty

**Warranty:** 10-Year Limited



## SPECIFICATION SUBMITTAL

|                                     |  |                      |
|-------------------------------------|--|----------------------|
| JOB NAME:<br><input type="text"/>   | CATALOG NUMBERS:<br><input type="text"/> |                      |
| JOB NUMBER:<br><input type="text"/> | <input type="text"/>                     | <input type="text"/> |

**Leviton Manufacturing Co., Inc.**

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)



**Visit our Website at: [www.leviton.com](http://www.leviton.com)**

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

*\*Leviton is the smart choice, providing the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial buildings. Leveraging more than a century of experience, Leviton helps customers create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, and lighting energy management systems. From switches and receptacles, to daylight harvesting controls, networking systems, and equipment for charging electric vehicles, Leviton solutions help customers achieve savings in energy, time and cost, all while enhancing safety.*