

Max. Extension:
13 3/4" (350mm)

L5038: Economy Metal Halide PAR Lampholder



L5038-70: 70W Electronic Ballast

L5038-100: 100W Electronic Ballast

Finish: White (P), Black (MB)

Lamp: 70W, 100W PAR38 Metal Halide

Accessories: L1964 Barn Doors,
L300 Series Color Filters




MB



P

Track System	Lampholder	Ballast	Finishes	Voltage	Accessories
	5038				
L=Halo and Lazer Track (except 4-Circuit Track) LA=Halo Architectural	5038=MH PAR38 Lampholder	70=70W Electronic Ballast 100=100W Electronic Ballast	P=White w/Black Baffle MB=Black	Blank=120V 277=277V (for Halo Architectural and RSA Busway Only)	L1964=Barn Doors L312=Warm Red Color Filter (use with L1964) L314=UV Filter (use with L1964) L320=Daylight Blue Color Filter (use with L1964) L330=Straw Color Filter (use with L1964) L331=Medium Amber Color Filter (use with L1964) L341=Medium Green Color Filter (use with L1964)




Max. Extension:
7 1/2" [191mm]

L4010 Colletto Roundback Cylinder

Finish: White (P), Black (MB), White with White Baffle (P/W)

Lamp: 50W PAR20, 75W PAR16

Accessories: L1971 Barn Doors




MB



P/W



P





Max. Extension:
7 3/4" [197mm]

L4011 Colletto Roundback Cylinder

Finish: White (P), Black (MB), White with White Baffle (P/W)

Lamp: 75W PAR30

Accessories: L1972 Barn Doors, L214 UV Filter
L200 Series Filters, L275 Louver
Barn door accessory allows use of filters, lenses or
louder.




MB



P/W



P





Max. Extension:
10" [254mm]

L4012 Colletto Roundback Cylinder

Finish: White (P), Black (MB), White with White Baffle (P/W)

Lamp: 150W PAR38

Accessories: L1964 Barn Doors, L314 UV Filter,
L300 Series Filters, L277 Louver
Barn door accessory allows use of filters, lenses, or
louder



MB



P/W



P

Lampholder/Track Compatibility

L4010 L4011 L4012	Halo Single and 2-Circuit L650, L651, L652, L653 L641, L642, L643 L611, L612, L613 L1631, L1632	Halo 4-Circuit L963 Converter required for use with Halo 4-Circuit: L621, L622, L623	Halo "LA" Architectural LA1L Converter required for use with Halo "LA" Linear Architectural Track: LA631, LA632, LA633	Lazer Track LZR102, LZR104, LZR106, LZR108
-------------------------	---	---	--	--