



Job Name:

Job Type:

Comments:

Quantity:

96119S-32: Lx LED Clear Festoon Lamp - 4000K 12v

Dimensions:



Bulb Appearance:

Gas Filled:

Bulb Type: LED

Bulb Base: festoon

Volts: 12

Watts: 0.6

Watts Consumed: 0.648

Watts Rated: 0.6

Hours Rated: 35000

Bulb Temp: 4000 °K

CRI: 85

Features:

- LED's energy savings and long life helps protect the environment by using less energy and keeping numerous other types of lamps, with shorter life, out of land-fills

Material List:

Safety Listing:

ETL Listed for Damp Locations
cETL Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1715FS)

It's a snap to upgrade existing xenon linear systems to energy saving, money saving lighting.
No need to replace or re-invest in your entire system.
The LED festoon is an opportunity to retrofit or replace traditional under-the-counter systems and fills the need to provide "green" lighting solutions.

Applications: Task & accent lighting for undercabinet, coves, toe-kick spaces and so much more. Directional nature of LED is ideal for in-cabinet lighting.

Retrofit/Remodel Installations for Magnetic Transformer Systems - JUST REPLACE THE LAMP!
Compatible as a retrofit for existing Lx xenon lamp and compatible xenon lamp systems.
Note: The unique design of the PCB (Printed Circuit Board) makes over voltage due to under capacity a non-issue.

Retrofit/Remodel Installations for Electronic Transformer Systems
60w zero-load LED driver available for replacing electronic transformers due to minimum load requirement. Available drivers: 96223S-12 & 96223S-15.

Product Features: Ease of installation. Ease of retrofit/remodel.
Bendable/flexibility of the system.

Dimmability: Dimmable with standard incandescent dimming switch.

A "Fit & Forget" Solution: Offering 35,000 hours of useful life (equivalent to 30 years at 20 hours of use per week)

Efficacy Warm White: 44 Lumens/Watt

Color Rendering: 4000K - CRI 85+

LED Festoon Product Line Options & Features:

12v and 24v
Warm (3000K)
Cool (4000K)
Clear lens for optimal performance
Frosted lens to reduce glare
Color-coded PCB to visually distinguish between warm and cool color
temperature LED festoons
Color-coded end-caps to identify 12v (white) and 24v (black)
3 Year Warranty

UPC #:785652028069

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	96119S-32	1	785652028069	2	2	0.75	0.002	0.001	Yes
Master Pack	96119S-32	10	10785652028066	9.25	2.38	1.18	0.015	0.2	Yes
NJ Pallet		25000		48	40	72	80	635	No
NV Pallet		25000		48	40	72	80	635	No