



Actual

**Catalog Number:** ST11/245-G  
**Product ID:** 7TAA087520R0004  
**UPC Number:** 70450840633  
**Status:** Active

PVC Coated Liquidtight Conduit Connector, 45 Degree, Pipe Size 1-1/2 Inch/41 Metric, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Steel Fitting, Dark Gray

- A minimum of .040 inch (40 mil) PVC coating is bonded to the exterior.
- Double coated with a nominal .002 inch (2 mil) blue urethane on both the interior and exterior, before PVC coating is applied.
- Pressure-sealing sleeves are designed to protect the connection.
- PVC coated connectors are available in straight, 45 degree and 90 degree configurations
- Ocal uses T&B Industrial Liquidtight fittings to insure quality installations.

#### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	Ocal
Type	Liquidtight Conduit Fitting - 45 Degree
Special Features	Pressure-Sealing Sleeves Protect the Connection
Application	To Positively Bond Conduit to Box or Enclosure
Size	1-1/2 Inch/41mm
Connection	45 Degree
Material	Steel
Finish	PVC Coated
Color	Dark Gray
Environmental Conditions	Hazardous Locations

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	41mm
Nominal size in inch	1 1/2 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Material housing	Steel
Surface protection	Other

#### Packaging

Inner Dimensions (inches)	xx
Outer Quantity	12
Outer Dimensions (inches)	14.75x7.75x8
Weight Uom	1.52 lbs. Each

#### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
860 Ridge Lake Blvd.

T&B Technical Support  
MS 3B-50

Hours: 7AM - 6PM CDT  
Monday-Friday

Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

860 Ridge Lake Blvd.  
Memphis, TN 38120

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)