



### 3124609-962: Nine Light Chandelier



**Collection:** Alturas

**UPC #:**785652108914

**Finish:** Brushed Nickel (962)

### Dimensions:

**Diameter:** 32 1/2"

**Height:** 32 5/8"

**Weight:** 21.1 lbs.

**Overall Height:** 77 1/8"

**Wire:** 144" (color/Clear Silver)

**Mounting Proc.:** Center Lock-Up

**Connection:** Mounted To Box

### Bulbs:

9 - Medium A19 60w Max. 120v - Not included

### Features:

- Easily converts to LED with optional replacement lamps
- Sloped ceiling mounting hardware included
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

### Material List:

- 1 Body - Steel - Brushed Nickel
- 1 6" Stem - Steel - Brushed Nickel
- 3 12" Stem - Steel - Brushed Nickel
- 1 Sloped Ceiling Hardware - Steel - Brushed Nickel

### Safety Listing:

Safety Listed for Damp Locations

### Instruction Sheets:

Trilingual (English, Spanish, and French) (990CH312460\_-ALT)

### Shade / Glass / Diffuser Details:

| Part  | Material | Finish                | Quantity | Item Number | Length | Width | Height | Diameter | Fitter Diameter | Shade Top Length | Shade Top Width | Shade Top Diameter |
|-------|----------|-----------------------|----------|-------------|--------|-------|--------|----------|-----------------|------------------|-----------------|--------------------|
| Shade | Glass    | Etched / White Inside | 9        | G560196-303 |        |       | 6 1/8  | 3 1/2    |                 |                  |                 |                    |

### Backplate / Canopy Details:

| Type   | Height / Length | Width | Depth | Diameter | Outlet Box Up | Outlet Box Down |
|--------|-----------------|-------|-------|----------|---------------|-----------------|
| Canopy | 3/4             |       |       | 5 1/8    |               |                 |

### Shipping Information:

| Package Type | Product #   | Quantity | UPC          | Length | Width | Height | Cube   | Weight | Frt. Class | UPS Ship |
|--------------|-------------|----------|--------------|--------|-------|--------|--------|--------|------------|----------|
| Individual   | 3124609-962 | 1        | 785652108914 | 35     | 39.5  | 20.25  | 16.201 | 28.1   | 300        | No       |
| NJ Pallet    |             | 3        |              | 48     | 40    | 72     | 80     | 84.3   |            | No       |
| NV Pallet    |             | 3        |              | 48     | 40    | 72     | 80     | 84.3   |            | No       |