

E26 5" Trim Series


DESCRIPTION

Frost dome glass lens trim with reflector and self-flange in the 5" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

- Low profile dome frost glass lens
- Wet location showerlight
- Torsion spring retention
- Non-conductive "Dead Front" plastic (polymer) trim ring and glass lens
- Socket supporting internal reflector
- Self-flanged trim ring sized to hide gaps caused by construction tolerances



Dimensions:

A: 4-1/2" [114mm]
H: 5-4/5" [148mm]
OD: 6-5/8" [168mm]

Housings	Max Lamp Compatibility
H5ICAT H5RICAT	29W A19, 39W PAR30S
E5ICAT E5RICAT	
H25ICAT	29W A19
H5ICATNB	29W A19, 39W PAR30S
E5ICATNB	
H25ICATNB	29W A19
H5T H5RT	60W A19, 50W PAR30S
E5TAT E5RTAT	
H5TNB	60W A19, 50W PAR30S
E5TATNB	

Compatible with Halogen, Incandescent, LED* or CFL* lamps.



5150WH

Frost Lens with Reflector,
White Plastic Trim



5150SN

Frost Lens with Reflector,
Satin Nickel Plastic Trim



5150TBZ

Frost Lens with Reflector,
Tuscan Bronze Plastic Trim

5150

5-Inch Frost Glass Lens,
Self-flange



ORDERING INFORMATION

SAMPLE NUMBER: 5130WH

Trim	Finish
5150= 5" Frost dome glass lens, self-flange	WH=Matte White plastic trim, self-flange SN=Satin Nickel plastic trim, self-flange TBZ=Tuscan Bronze plastic trim, self-flange

HALO HOUSING COMPATIBILITY

Trim #	Style	H5ICAT	H5RICAT	E5ICAT	E5RICAT	H25ICAT	H5ICATNB	E5ICATNB	H25ICATNB
5150	Showerlight	•	•	•	•	•	•	•	•
		H5T	H5RT	E5TAT	E5RTAT	H5TNB	E5TATNB		
		•	•	•	•	•	•		

For use in other's housings, refer to U.L. Classification list at www.eaton.com/lighting/legal.

*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Eaton does not warranty the lamp.



For use in Halo listed housings.



Select trims are classified for use in others housings.
See www.eaton.com/lighting/legal.