



GE  
Lighting

## 62402 - Integrated 4ft LED Plastic Tubes

### LED15ET8/4/840

- ☞ Convert your existing linear fluorescent fixture to LED lighting without needing a comprehensive reinstall.
- ☞ LED tubes are ideal for those seeking high energy savings with minimal installation time.
- ☞ Each LED tube is outfitted with an internal GE driver.
- ☞ GE integrated LED tubes run on electronic T8 instant-start or programmed start ballasts.
- ☞ Shatter resistant
- ☞ No UV
- ☞ Easy disposal, non-hazardous waste
- ☞ NSF Rated for food application (shatter resistant)
- ☞ UL Listed
- ☞ DLC Listed

### Product Photo



### GENERAL CHARACTERISTICS

Dimmable	Yes
Product Technology	LED
Rated Life (Hours)	50000 h
Dimmable / Non-Dimmable	Yes
LED Tube Type	Plastic
10 Digit U	4316862402
Lamp Count	1
Life in Years	45.7 yr
Replacement Watts	0 W
Requested Structure	Sleeve
Estimated Energy Cost per Year	1.81
Base	G13
Bulb Shape	T8

### PHOTOMETRIC CHARACTERISTICS

Initial Lumens-nominal	2250 lm
Color Rendering Index-CRI	80
Color Temperature	4000 K

### PRODUCT INFORMATION

Product Code	62402
Description	LED15ET8/4/840
Alternative Unit Of Measure	CASE
Standard Package Quantity	25
Ean UPC	043168624022
Standard Package GTIN	10043168624029
No Of Items Per Sales Unit	
No Of Items Per Standard Package	25
Sales Unit	Case
UCC	043168624022
Alternative Unit Of Measure	EACH
Standard Package Quantity	25
Ean UPC	043168624022
Standard Package GTIN	00043168624022
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	25
Sales Unit	Each
UCC	043168624022

### DIMENSIONS

Bulb Max Overall Length-MOL	48.0 in
-----------------------------	---------

### ELECTRICAL CHARACTERISTICS

Rated power (Watts)	15 W
---------------------	------

### CAUTIONS & WARNINGS

#### Caution

##### Risk of fire

Use only in place of fluorescent lamps specified on label

If the lamp or luminaire exhibits undesirable operation, immediately turn off power, remove lamp from luminaire and contact manufacturer

Direct replacement for 25W/48T8, 28W/48T8, 30W/48T8, 32W/48T8 lamps only

Do not install this lamp in a pre-heat luminaire

This lamp only operates on electronic ballasts

If lamp does not light when luminaire is energized, remove lamp from luminaire and contact lamp manufacturer or qualified electrician