

7" Low Profile Flushmount

11.5 Watts 810lms LED 54663142
Part# FM-7-11-840-SV-N-0

SPECIFICATIONS




The ETI 11.5 Watts 810 lumen LED 7" Low Profile light is an ideal wall and ceiling mounted work light. Designed to replace a standard work light with a 60W incandescent lamp. They are UL listed for use in damp and dry locations. Warranty 5 years. Suitable for installations from - 4° F to 95° F.

Designed to be used anywhere a standard incandescent fixture is used. Typically used in bedrooms, hallways, kitchens, living rooms and recreational rooms. Other applications apply in commercial, office, retail, restaurants, schools, hospitals and hotel/motel locations.

KEY FEATURES & BENEFITS

11.5 Watts
120V
810 lumen, 4000K CCT
Non-dimmable
UL damp location rated
No UV, IR or mercury
Warranty for 5 years

FIXTURE DIMENSIONS



Part# FM-7-11-840-SV-N-0
Dimension A =7.0"
Dimension B =2.0"

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, Please see www.etissl.com/fcc15b

www.etissl.com
855-384-7754



7" Low Profile Flushmount

11.5 Watts 810lms LED 54663142
Part# FM-7-11-840-SV-N-0

SPECIFICATION DATA

Item Number	Description	Watts	Input Voltage (VAC)	Average Rated Life ¹	Typical Lumens ²	CCT ³	CRI ⁴	Power Factor	R9	DUV	CBCP	Beam Angle	Operating Frequency
54663142	7" Low Profile-MV, Non Dim	11.5	120	50,000 hours	810	4000K	80	>0.98 @120V	12	/	/	120	60Hz
¹ Hours lifetime with 70% lumen maintenance													
² Thermally stable typical lumens													
³ in compliance with ANSI C77.378 201X													
⁴ Color rendering index/Ra													

SHIPPING INFORMATION

Item Number	Item UPC	Item Dimensions (H x L x W)	Item Weight (lbs)	Inner Pack Qty	Inner Carton Bar Code	Inner Carton Dimensions (H x L x W)	Inner Pack Weight (lbs) Dimensions (H x L x W)	Master Pack QTY	Master Carton Bar Code	Master Dimensions (H x L x W)	Master Pack Weight (lbs)
54663142	84948900 0626	15.4" x 15.4" x 2.95"	1.84	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A



The Americas Headquarters
720 Corporate Woods Parkway
Vernon Hills, IL 60061
855-384-7754
www.etissl.com

