


2' x 2' Flat Panel

LED 54320141

42.5 Watt, 4000K, 4250 lumen



The ETi LED 42.5 Watt 4250 lumen 2' x 2' flat panel LED fixture provides exceptional performance and market leading quality. Designed to mount as a drop in panel or suspension mounted, standard. The panels can also be mounted flush with an additional accessory piece. They are UL listed for use in damp and dry locations, are IC rated and are RoHS compliant with no lead or mercury. Warranty period 5 years or 60 months. Suitable for installations from -4° F to 113° F.

KEY FEATURES & BENEFITS

- 42.5 Watt
- 4250 Lumens
- Dimmable 0-10V
- >80 CRI, 4000K Cool White
- No UV, IR or mercury
- UL - Damp Location

Rated Lifetime: 78,000 hours

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, please see www.etissl.com/fcc15b

DIMENSIONS

SKU# 54320141

Length = 23.74"

Width = 23.74"

Height = 0.9"



APPLICATION INFORMATION

ETi SSL offers the Commercial Grade Flat Panel which is approved for all drop tile ceiling types can be directly suspended or flush-mounted. Typical applications include; offices, academies, universities, retail locations, lobbies as well as residential settings.



855-384-7754 www.etissl.com

42.5 Watt 4250lms 2' x 2' Flat Panel

LED

54320141

SPECIFICATION DATA

Project _____

ItemNumber _____

Prepared by _____ Date _____

ORDERING INFORMATION

Item Number	Description	Wattage	Input Voltage (VAC)	Average Rated Life ¹	Typical Lumens ²	CCT ³	R9	Duv	CRI ⁴	Power Factor	0-180 Spacing	90-270 Spacing	Operating Frequency
54320141	2'x2' Flat Panel	42.5	120-277	80,000 hrs	4250	4000K	15	.0003	>80	>0.95	1.26	1.26	50/60Hz
TBD	Earthquake Clips (2)												
TBD	Flushmount mounting plate(1)												

¹ Hours lifetime with 70% lumen maintenance

² Thermally stable typical lumens ($\pm 10\%$)

³ Thermally stable CCT ($\pm 10\%$)

⁴ Color rendering index/Ra

SHIPPING INFORMATION

Item Number	Item UPC	Item Dimensions (L x W x H)	Item Weight (lbs)	Inner Pack Qty	GTIN NO	
54320141	849489005225	23.74"x23.74"x0.9"	8.97	1	50849489005220	



The Americas Headquarters
720 Corporate Woods PKWY
Vernon Hills, IL 60061

855-384-7754 www.etissl.com