



SPECIFICATION SHEET

Reflector Dimmable LED Lamp

Item Number **05155**

Specifications

Energy Used (Watts).....	6
Incandescent Equivalent Wattage.....	45
Domestic Code.....	6R16/LED/DIM/FL/27 1CD
Volts.....	120
Brightness (Lumens).....	450
Average Rated Hours.....	25,000
Life (in years)*.....	22.8
Light Appearance (Kelvin).....	2700
Beam Type.....	Flood
Beam Spread.....	105°
CRI.....	80
Efficacy (LPW).....	75
Number of LED Modules.....	6
Estimated Yearly Energy Cost**.....	\$0.72
Package Type.....	Card



Physical Characteristics

Color Designation.....	Warm White
Finish.....	Frost
Housing Material.....	Aluminum/Plastic
Base.....	Medium
MOL.....	3.23"



Limited Warranty

This lamp is warranted to be free from defects in material and workmanship for 5 years (based on using 3 hours per day).

Warning

- Turn power off before inspection, installation, or removal.
- Risk of electric shock - Do not use where exposed to water or weather.
- Suitable for Damp Locations - The lamp is suitable for use in wet locations when used in an outdoor rated fixture.
- Not for use in totally enclosed fixtures.
- Do not open – no user serviceable parts inside.
- This device is not intended for use with emergency exit luminaires or emergency exit lights.
- This device complies with Part 15 of the FCC rules and has been tested and found to comply with the limits for a Class B digital device. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. Any changes or modifications not expressly approved by the manufacturer could void the user's authority to operate the equipment.
- This lamp may not be compatible with all dimmers.

*Based on 3 hrs./day

** Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

REFLECTOR LED Dimmer Compatibility

Brand	Model
Leviton	6161, 1P106-1LZ/-96, 1PL06-10Z/-92, C20-06681-12A, RTDP1/jsb-100
Lutron	DIVA DVCL-153P, MAELV-600, SYLNRK SELV-300P, Radio RA2 RRD-6NA, DIVA DVELC-303P-WH, SYLNRK CTELV-303P, Lumea LGCL-153P, SYLNRK S-600P, SYLNRK CTCL-153P, Lumea LGCL-153PL, VTELV-600M, VETLV-VTELV-600M-B-WH, S-603P-WH, DV-603P-WH, NTLV-600-WH/-88, LGCL-153PLH-WH, LUTRO-S-600P-WH

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

®. WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.

Used under license by Westinghouse Lighting. All Rights Reserved.