



Multiple Voltage
120-277V



Optional Pull Chain



Optional
Battery Back Up



FMM

Flush Mount Modern

18W, 22W, 26W

Our FMM series ceiling light is perfect for kitchens and open areas, hallways, bedrooms and any decorative lighting. Brighten your room with our energy efficient LED with our FMM ceiling.

The design features low-profile body with nickel finish accents and a white acrylic diffuser. Available in 3 sizes and replaces up to 200 watt incandescent bulbs. Optional pull chain and battery back up for multiple voltage model.

Key Features & Benefits

- ▶ Easy Installation
- ▶ Energy Star Certified
- ▶ Uniform light distribution and consistent color
- ▶ Instant On
- ▶ Non-yellowing acrylic
- ▶ CRI: 80
- ▶ Dimmable
- ▶ 50,000 hrs rated average life

Applications

- ▶ Kitchen Lighting
- ▶ Decoration Lighting
- ▶ Hallway Lighting
- ▶ Bedroom Lighting

Color Choices




Nickel

Qualifications



ORDERING INFORMATION

2

Item Code	Description	Color Temp	Wattage	Lumen Output	Equivalent Wattage	Size	Voltage (V)	Rated Hours	Dimmable		
120V	7430	LED12FMM-138L830-NI	3000K	18	1,380	120	12-inch	120	50,000	•	•
	7431	LED12FMM-138L840-NI	4000K	18	1,380	120	12-inch	120	50,000	•	•
	7433	LED14FMM-165L830-NI	3000K	22	1,652	150	14-inch	120	50,000	•	•
	7434	LED14FMM-165L840-NI	4000K	22	1,652	150	14-inch	120	50,000	•	•
	7533	LED16FMM-196L830-NI	3000K	26	1,960	200	16-inch	120	50,000	•	•
	7534	LED16FMM-196L840-NI	4000K	26	1,960	200	16-inch	120	50,000	•	•
120-277V	7596	LED12FMM-138L840-NI/MV	4000K	18	1,380	120	12-inch	120	50,000	1-10V	•
	7597	LED14FMM-165L840-NI/MV	4000K	22	1,652	150	14-inch	120	50,000	1-10V	•
	7598	LED16FMM-196L840-NI/MV	4000K	26	1,960	200	16-inch	120	50,000	1-10V	•




Accessories

P10077	SWCH-ZE109-NI	Pull String Switch Nickel
7332	BAEM8.4-60/MV-B	Emergency Battery Backup Driver

► Dimensions

	Size	A	B	C	Weight (lbs)
	12-inch	12.00-in	3.35-in	4.25-in	1.96
	14-inch	14.00-in	3.35-in	4.25-in	2.49
	16-inch	16.00-in	3.35-in	4.25-in	3.01

► Illuminance Distribution



► Master Carton Package

