



Hazardous Location Fittings-PVC Coated

T&B Catalog Number:

UPC Number: EYS21-G
70450837364
Status: Active
Description:

PVC Double-Coated Conduit Sealing Fitting, EYS Series for Hazardous Locations, for Sealing in Vertical or Horizontal Positions, Female Hub, Hub Size 3/4 Inch/21 Metric, Turning Radius 1.25 Inch/31.75 Millimeters, Ductile Iron, Gray

Features

All hubs have a minimum of five full threads, integral bushings to protect conductor insulation from damage, and large access openings for easier packing of sealing material.

Seals are approved to be used with Crouse Hinds® Sealing Compound and Fiber.

Application

Restricts the passage of gases, vapors and flames at atmospheric pressure and normal ambient temperatures

General

Trade Size (inches)	3/4
Material	Ductile Iron
Finish	PVC Coated
Color	Dark Gray

Dimension Information

Pipe Size (inches)	3/4
Pipe Size (Metric Size Designator*)	21
Hub Size (inches)	3/4
Dimension A (inches)	3.66
Dimension B (inches)	1.50
Turning Radius (inches)	1.25

Technical Information

Chemical Resistance Chart	Available on Website
---------------------------	----------------------

Specifications

Ocal Specification Guide-1995 Master Format-PDF	Available on Website
Ocal Specification Guide-1995 Master Format-DOC	Available on Website
Ocal Specification Guide-2004 Master Format-PDF	Available on Website
Ocal Specification Guide-2004 Master Format-DOC	Available on Website

Packaging

Package in Units	20
------------------	----

T&B Sold in UOM	Each
T&B Weight Per UOM	1.25 lbs. Each

Application Support

Ocal Specifications	Available on Website
Recommended Installation Procedures	Available on Website
Product Overview-Conduit Outlet Bodies	Available on Website
NEMA Standards-RN 1	Available on Website
NEC 310-16 - Conductors for General Wiring	Available on Website
NEC Table 8	Available on Website

Notes

Metric size designator (ANSI C80. 1-1994)

Dimensions are of uncoated fittings

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E 193396

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com