



EVOLUTION 6AT2P SERIES RECESSED PREWIRED ASSEMBLY WITH FLUSH STYLE COVER

6AT2P | [Wiremold](#)

FEATURES & BENEFITS

For tile, wood and laminate concrete floor coverings. For use in 6" (152mm) diameter opening. Devices are recessed 3 1/4" (83mm) below floor surface. Die-cast aluminum cover assembly is available in the following powder coated finishes: (BK) black, (GY) gray, (NK) nickel, (BS) brass, (BZ) bronze, and (AL) aluminum. INCLUDED: For Side Compartments: Two (2) proprietary 20A Duplex Receptacles installed. For Center Compartment: One (1) 6ACT8A Mounting Plate, One (1) 6TRAC Mounting Plate, One (1) 6SER Mounting Plate. For Bottom Feed Compartment: One (1) 5BLH 1/2-Gang Blank Housing (Tunneling extends from the 5BLH to 575CHA so that power cables from the 20A duplex receptacle mounted on the left side of the poke-thru device are run into the junction box attached to the 575CHA.), One (1) 1PTHA 1-Gang Pass-Through Housing Assembly, One (1) 575CHA 1/2-Gang 3/4" Conduit Housing Assembly (also includes junction box attached to the 3/4" conduit). NOTE: UL Fire Classified for up to 2-hour rated floors. Receptacles can be wired as a standard or isolated ground device. Includes one (1) 6TS Tile Shim.



- **Aluminium cover assemblies.** The Evolution Series poke-thru design includes all metal die-cast aluminium cover assemblies, with two unique spring-loaded slide egress doors. Available in surface style and flush style in standard finishes of brass, gray, black, nickel, bronze, and aluminium offering a wider range of aesthetic options.
- **Meets ADA Accessibility Guidelines.** Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.
- **UL Listed and UL Fire Classified to U.S. and Canadian safety standards.** UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.
- This product meets the material restrictions of RoHS

SPECIFICATIONS

GENERAL INFO

Available Colors:

6AT2PGY - Gray

6AT2PBK - Black

6AT2PBS - Brass

6AT2PBZ - Bronze

6AT2PNK - Nickel

6AT2PAL - Aluminum

Product Series: Evolution

Type: Multi-Service

Component Type: Full Assemblies

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Hole Size: 6"

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MULTIPLE

Buy American Act Status: No