



Catalog Number: 88L90C
Item Description: WIREWAY ACCESSORY
UPC Code: 784572109933


Brand Name: Milbank
Type: Wireway 90 Degree Side Access Elbow
Application: Wireway Accessory
Standard: UL Listed, Type 1
Cover Type: Screw Cover
Enclosure: Indoor Enclosure
Nominal Cross Section: 8x8
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False




Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

CATALOG#	LABEL#
88L90C	1002943
RC-88L90C	1125051

BILL OF MATERIAL		
NO.	QTY.	DESCRIPTION
1	1	PLATE (IN) #(SEE CHART)
2	1	PLATE (OUT) #(SEE CHART)
3	2	SIDE #(SEE CHART)
4	10	SCREW 10-32 #1001290
5	1	U/L LABEL (SEE CHART)
6	1	LABEL, RATING #1002913



SUFFIX	FINISH	PLATE (IN)	PLATE (OUT)	SIDE
NONE	MILBANK LIGHT GRAY	1159991	1159990	1159989
-NP	NONE	1002268	1002266	1002264



NEMA DWG.: #536

REVISIONS:

A	2-26-96	ADD (2) SCREWS	DWD	S			REMOVED NOTE#1			B	5/27/11	1001290 (10) WAS (8)			C	12/10/13	WAS DWG#536		
A1	9-20-06	mECO #15183					ECO.17139	JLT	E			(ECO #20744)	D.F.	F4			eECR0002604	SEM	P4
		ADDED NOTE #1	CMW	S	A3	7/7/09	UPDATE TO M2K			B1	7/12/12	CHART FINISH			D	1/3/14	ADD #6(eECR2642)	SEM	P4
A2		ADDED CHART &					(ECO #18436)	D.F.	F4			(ECO #22618)	D.F.	F4					

MATERIAL:	16 GA. STL.
FINISH:	SEE CHART
CATALOG NO:	SEE CHART
TITLE:	SCREW COVER WIREWAY 90 DEGREE ELBOW
CUSTOMER:	MILBANK STD.
DRAWING NO:	1002572
MILBANK MFG. CO.	
KANSAS CITY, MO. KOKOMO, IN.	
DRAWN BY: VJR	SCALE: NTS
CHECKED BY: SEM	DATE: 5-15-90
APPROVED:	