



Powering Business Worldwide

pe.eaton.com

Eaton Series C electronic molded case circuit breaker

FDE308036

UPC:786685112336

Dimensions:

- **Height:** 6 IN
- **Length:** 3.38 IN
- **Width:** 4.13 IN

Weight:4.5 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 80A
- **Interrupt Rating:** 65 kAIC at 240 Vac, 35 kAIC at 480 Vac
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600 Vac, 250 Vdc
- **Trip Type:** Electronic LSIG
- **Circuit Breaker Type:** FDE
- **Circuit Breaker Frame Type:** Complete breaker
- **Frame Size:** F-frame
- **Series:** Series C
- **Terminals:** Load side
- **Frequency Rating:** 50/60 Hz

Supporting documents:

- [Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)
- [UL listed 100%-rated molded case circuit breakers](#)
- [Application of Tap Rules to Molded Case](#)



Breaker Terminals

- [MOEM MCCB Product Selection Guide](#)
- [Current limiting Series C molded case circuit breakers product aid](#)
- [Circuit breaker motor operators product aid](#)
- [Plug-in adapters for molded case circuit breakers product aid](#)
- [StrandAble terminals product aid](#)
- [Motor protection circuit breakers product aid](#)
- [Power metering and monitoring with Modbus RTU product aid](#)
- [Multi-wire lugs product aid](#)
- [Molded case circuit breakers](#)
- [Eatons Volume 4-Circuit Protection](#)
- [F-frame Molded Case Circuit Breaker Drawing](#)
- [Time Current Curves for Series C® F-Frame Circuit Breakers](#)
- [Installation Instructions for Series C F-Frame Circuit Breakers](#)
- [Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)
- [Counterfeit and Gray Market Awareness Guide](#)
- [Breaker service centers](#)
- [MOEM MCCB product selection guide](#)
- [Series C G-Frame molded case circuit breakers time current curves](#)
- [Series C J-Frame molded case circuit breakers time current curves](#)
- [Series C F-Frame molded case circuit breakers](#)
- [F-Frame 310+ Molded-case circuit breakers 15-225A](#)

Certifications:

- [UL Listed](#)

Product compliance: No Data