





Catalog Number: 2212-GSC1
Item Description: N1 SCREW CVR GUTTER
UPC Code: 784572265981

Brand Name: Milbank
Type: Lay In Wireway
Application: Wireway
Standard: UL Listed, Type 1
Cover Type: Screw Cover
Enclosure: Indoor Enclosure
Nominal Cross Section: 2x2
Straight Section Length: 12
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: True



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

CATALOG#	LABEL#
2212-GSC1()	1002943
RC-2212-GSC1()	1125051
SPS-221()	1132575





NOTE:
1. PLACE BAG ASS'Y INSIDE ENCLOSURE. (NOT SHOWN)

ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK
2	1	(SEE CHART)	PLATE
3	1	(SEE CHART)	UL LABEL, WIREWAY
4	1	1095339	LABEL, RATING
5	4	1001290	SCREW, 10-32 X 5/16
6	1	1002880	BAG ASSY (NOT SHOWN)

SUFFIX	MATERIAL	FINISH	BACK NO.	PLATE NO.	INSTALL KOs
NONE	16 GA. GALV. STEEL	MILBANK LIGHT GRAY	1153506	1153503	YES
-NP		NONE	1129397	1129385	YES
-NK		MILBANK LIGHT GRAY	1129399	1153503	NO
-NK-NP		NONE	1153505	1129385	NO

SUFFIX	MATERIAL	FINISH	BACK NO.	PLATE NO.	INSTALL KOs
NONE	16 GA. CRS	MILBANK LIGHT GRAY	1129396	1129384	YES
-NP		NONE	1129395	1129382	YES
-NK		MILBANK LIGHT GRAY	1129400	1129384	NO
-NK-NP		NONE	1129398	1129382	NO



Material:		16 GA. - SEE CHART		 General Offices: Kansas City, MO	
Finish:		SEE CHART			
Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X" ±2°		 Third Angle Projection		Title:	SCREW COVER WIREWAY 2 x 2 x 12, TYPE 1 ENCLOSURE
				Catalog No.:	(SEE CHART)
				Customer:	MILBANK STANDARD
				Drawing No.:	1004269
F.	Scale:	NTS	Checked By:		
F.	Drawn By:	DY	Approved By:		Date: 02/19/03 Sheet 1 of 1

NEMA DWG.: #11277