

2660



Color: Black

UPC Code: 07847704586

Country Of Origin: Mexico

**Eligible for ARRA funded projects > \$7,443,000*

NEMA:
L10-30R



2660

Item Description

30 Amp, 125/250 Volt, NEMA L10-30R, 3P, 3W, Flush Mtg Locking Receptacle, Industrial Grade, Non-Grounding, V-0-MAX - BLACK

Technical Information

AC Horsepower Ratings

At Rated Voltage: 2 HP L-L / 2 HP L-N

Electrical Specifications

Dielectric Voltage: Withstands 2000V per UL498

Grounding: Non-Grounding

Temperature Rise: Max 30C after 250 cycles OL at 200 percent rated current

Voltage: 125/250 Volt

Amperage: 30 Amp

Current Limiting: Full Rated Current

Wire: 3

Pole: 3

Environmental Specifications

Operating Temperature: -40C to 60C

Flammability: Rated V-0 per UL94

Material Specifications

Strap Material: Nickel-Plated Brass

Face Material: Nylon

Body Material: Nylon

Terminal Screws: Chromated Brass

Ground Contacts: Brass

Color: Black

Cover Material: Valox 357

Line Contacts: Brass

Yoke: Nickel-Plated Brass .050 Thick

Grounding Screw: Chromated Brass

Terminal Clamps: Nickel-Plated Brass

Base Material: Nylon

Mechanical Specifications

Product ID: Ratings and NEMA I.D. permanently marked on device

Terminal ID: Marked on Device

Termination: Back & Side

Terminal Accom.: 14-8 AWG

Product Features

Face Material: Nylon

Warranty: Lifetime Limited

Color: Black

Standards and Certifications: UL

Base Material: Nylon

NEMA: L10-30R

Standards and Certifications

CSA: C22.2 No. 42

UL: 498

ANSI: C-73


NOM: 057

UL Fed Spec: W-C-596


NEMA: WD-1 & WD-6

Warranty

Warranty: Lifetime Limited



Wiring Diagram



SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
JOB NUMBER:		

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/



**Leviton is the smart choice, providing the most comprehensive range of solutions to meet the needs of today's residential, commercial and industrial buildings. Leveraging more than a century of experience, Leviton helps customers create sustainable, intelligent environments through its electrical wiring devices, network and data center connectivity solutions, and lighting energy management systems. From switches and receptacles, to daylight harvesting controls, networking systems, and equipment for charging electric vehicles, Leviton solutions help customers achieve savings in energy, time and cost, all while enhancing safety.*