



## Conduit Fittings-PVC Coated

**T&B Catalog Number:**

ST3/445-G

**UPC Number:**

70450840760

**Status:**

Active

**Description:**

3/4 in. Dark Gray PVC Coated 45 degree Liquidtight Connector. Fitting material-Steel.

### Features

A minimum of .040 in. (40 mil) PVC coating is bonded to the exterior.

Double coated with a nominal .002 in. (2 mil) blue urethane on both the interior and exterior, before PVC coating is applied.

Pressure-sealing sleeves are designed to protect the connection.

PVC coated connectors are available in straight, 45 degree and 90 degree configurations

Ocal uses T&B Industrial Liquidtight fittings to insure quality installations.

### Application

To positively bond conduit to box or enclosure

### General

Custom_Finish	lt_34_45
Trade Size (inches)	3/4
Material	Steel
Finish	PVC Coated
Color	Dark Gray

### Dimension Information

Pipe Size (Metric Size Designator*)	21
Dimension A (inches)	1 21/32
Dimension B (inches)	2 1/8
Dimension C (inches)	9/16

### Technical Information

Chemical Resistance Chart	Available on Website
---------------------------	----------------------

### Specifications

Ocal Specification Guide-1995 Master Format-PDF	Available on Website
Ocal Specification Guide-1995 Master Format-DOC	Available on Website
Ocal Specification Guide-2004 Master Format-PDF	Available on Website
Ocal Specification Guide-2004 Master Format-DOC	Available on Website

### Packaging

Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	0.46 lbs. Each

### Application Support

Ocal PVC Coated Conduit System	Available on Website
--------------------------------	----------------------

Ocal Specifications	Available on Website
Recommended Installation Procedures	Available on Website
Product Overview-Conduit Outlet Bodies	Available on Website
NEMA Standards-RN 1	Available on Website
NEC 310-16 - Conductors for General Wiring	Available on Website
NEC Table 8	Available on Website

## Notes

Dimensional values are of uncoated liquidtight fittings.

Metric size designator (ANSI C80. 1-1994)

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com