



8883-08: Two Light Outdoor Wall Lantern



Collection: Jamestowne

Large Two Light Outdoor Wall Sconce in Textured Rust Patina. Clear Seeded Glass Accents Classic Simplicity.

A warm and natural finish of textured rust patina over solid brass and clear seeded glass delivers timeless charm.

UPC #:785652888380

Finish: Textured Rust Patina (08)

Dimensions:

| | | | |
|----------------|----------|-------------------------|----------------|
| Width: | 7" | Extends: | 7 3/4" |
| Height: | 20 1/4" | Wire: | 6 1/2" |
| Weight: | 5.2 lbs. | Mounting Proc.: | Cap Nuts |
| | | Connection: | Mounted To Box |
| | | Bulb Appearance: | Clear |

Bulbs:

2 - Candelabra Torpedo 40w Max. 120v - Not included

Features:

- Clear bulb(s) recommended for this fixture
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

- 1 Body - Aluminum - Textured Rust Patina
- 1 Bracket - Aluminum - Textured Rust Patina
- 1 Canopy - Aluminum - Textured Rust Patina
- 1 Candle Cover - Aluminum - Textured Rust Patina

Safety Listing:

Safety Listed for Wet Locations
Safety Listed for Wet Locations

Instruction Sheets:

English (HC-231)
French (F-009)

Shade / Glass / Diffuser Details:

| Part | Material | Finish | Quantity | Item Number | Length | Width | Height | Diameter | Fitter Diameter | Shade Top Length | Shade Top Width | Shade Top Diameter |
|-------|----------|--------------|----------|-------------|--------|--------|----------|----------|-----------------|------------------|-----------------|--------------------|
| Panel | Glass | Clear Seeded | 4 | | | 5 7/16 | 11 15/16 | | | | | |

Backplate / Canopy Details:

| Type | Height / Length | Width | Depth | Diameter | Outlet Box Up | Outlet Box Down |
|------------|-----------------|-------|-------|----------|---------------|-----------------|
| Back Plate | 5 1/2 | 4 3/4 | 3/4 | | 6 1/2 | 13 3/4 |

Shipping Information:

| Package Type | Product # | Quantity | UPC | Length | Width | Height | Cube | Weight | Fr. Class | UPS Ship |
|--------------|-----------|----------|--------------|--------|-------|--------|-------|--------|-----------|----------|
| Individual | 8883-08 | 1 | 785652888380 | 8.75 | 8.5 | 21.25 | 0.915 | 6.5 | 125 | Yes |
| NJ Pallet | | 72 | | 43.5 | 36 | 71.25 | 64.57 | 468 | | No |
| NV Pallet | | 72 | | 43.5 | 36 | 71.25 | 64.57 | 468 | | No |