


NTS-871 Open Reflector

DIMENSIONS



FEATURES

Reflector

Precision spun 0.050 aluminum high grade reflector with white or self flanged.

Mounting

Two keyhole slots are on the top of the reflector to allow frame-in screws to secure reflector.

Compatible Frame-Ins

NTS-871 is compatible with Compact Fluorescent frame-ins.
See individual specification sheets for more information.

Lamp

Compact Fluorescent

(1-2) 13W-26W Quad (NHP8U Series; NH8PU Series; NHR8PU Series)
(1-2) 13W-42W Triple (NHP8U Series; NH8PU Series; NHR8PU Series)

Compact Fluorescent Emergency Frame-In

NTS-871 is compatible with Compact Fluorescent frame-ins with emergency integral test switch. Add suffix "/EM" to item number when used with frame-in with emergency integral test switch.

Listing

cULus Listed for Damp Location when used with Compatible Frame-Ins

NORALIGHTING.

Type

Project

Catalog No.

Lamp/Wattage

Compatible Frame-Ins

COMPACT FLUORESCENT

Item Number	Installation Type	Lamp	Dimensions
NHP8U-113EL	Universal Brackets	(1) 13W Quad/Triple	W: 13-1/4" L: 16" H: 6-1/2"
NHP8U-118EL	Universal Brackets	(1) 18W Quad/Triple	W: 13-1/4" L: 16" H: 6-1/2"
NHP8U-12642EL	Universal Brackets	(1) 26-42W Quad/Triple	W: 13-1/4" L: 16" H: 6-1/2"
NHP8U-213EL	Universal Brackets	(2) 13W Quad/Triple	W: 13-1/4" L: 16" H: 6-1/2"
NHP8U-218EL	Universal Brackets	(2) 18W Quad/Triple	W: 13-1/4" L: 16" H: 6-1/2"
NHP8U-22642EL	Universal Brackets	(2) 26-42W Quad/Triple	W: 13-1/4" L: 16" H: 6-1/2"
NH8PU-113EL	24-1/2" Bar Hangers	(1) 13W Quad/Triple	W: 13-1/4" L: 14" H: 6-1/2"
NH8PU-118EL	24-1/2" Bar Hangers	(1) 18W Quad/Triple	W: 13-1/4" L: 14" H: 6-1/2"
NH8PU-12642EL	24-1/2" Bar Hangers	(1) 26-42W Quad/Triple	W: 13-1/4" L: 14" H: 6-1/2"
NH8PU-213EL	24-1/2" Bar Hangers	(2) 13W Quad/Triple	W: 13-1/4" L: 14" H: 6-1/2"
NH8PU-218EL	24-1/2" Bar Hangers	(2) 18W Quad/Triple	W: 13-1/4" L: 14" H: 6-1/2"
NH8PU-22642EL	24-1/2" Bar Hangers	(2) 26-42W Quad/Triple	W: 13-1/4" L: 14" H: 6-1/2"
NHRP8U-113EL	Remodel	(1) 13W Quad/Triple	W: 8-1/2" L: 13" H: 7-1/2"
NHRP8U-118EL	Remodel	(1) 18W Quad/Triple	W: 8-1/2" L: 13" H: 7-1/2"
NHRP8U-12642EL	Remodel	(1) 26-42W Quad/Triple	W: 8-1/2" L: 13" H: 7-1/2"
NHRP8U-213EL	Remodel	(2) 13W Quad/Triple	W: 8-1/2" L: 13" H: 7-1/2"
NHRP8U-218EL	Remodel	(2) 18W Quad/Triple	W: 8-1/2" L: 13" H: 7-1/2"
NHRP8U-22642EL	Remodel	(2) 26-42W Quad/Triple	W: 8-1/2" L: 13" H: 7-1/2"

Open Reflector

NTS-871LISF: Low Iridescent Alzak® Clear Reflector with Self Flange

NTS-871LISF/EM: Low Iridescent Alzak® Clear Reflector, Self Flanged for Integral Test Switch

NTS-871LIWF: Low Iridescent Alzak® Clear Reflector with White Flange

NTS-871LIWF/EM: Low Iridescent Alzak® Clear Reflector, White Flange for Integral Test Switch

NTS-871B: Specular Black Reflector with White Flange

NTS-871B/EM: Specular Black Reflector with White Flange for Integral Test Switch

NTS-871C: Specular Clear Reflector with White Flange

NTS-871C/EM: Specular Clear Reflector with White Flange for Integral Test Switch

Designer Alzak® Finishes:

B - Black, BZ - Bronze, CG - Champagne Gold, G - Gold, HZ - Haze, PE - Pewter, ST - Straw, WH - Wheat

NTS-871CLIWF: Low Iridescent Clear Reflector with White Flange

NTS-871CLIWF/EM: Low Iridescent Clear Reflector with White Flange for Integral Test Switch

NTS-871G: Specular Gold Reflector with White Flange

NTS-871G/EM: Specular Gold Reflector with White Flange for Integral Test Switch

NTS-871W: Specular White Reflector with White Flange

NTS-871W/EM: Specular White Reflector with White Flange for Integral Test Switch

NTS-871CLISF: 1 Low Iridescent HORZ Clear Reflector, Self Flange

NORALIGHTING.

6505 Gayhart St., Commerce, CA 90040
www.noralighting.com • Specifications subject to change without notice. © 2011
Phone: 800.686.6672 • FAX: 800.500.9955 • e-mail: nora@noralighting.com