

39005	5/16x1-3/4 HEX TEK DRIVER BIT
--------------	--------------------------------------

UPC: 085937390059 Country of Origin: TAIWAN
 UNSPSC: 27112815
 Commodity: Nut driver bits

5/16 x 1-3/4" Hex Driver Bits, #10-12 Screw, Magnetic

Product Attributes	
Brand Name	Minerallac Company
Sub Brand	ITM
Type	Hex Tek Driver Bit
Special Features	Magnetic
Application	5/16" Hex Driver Bit
Drive Size	5/16" IN
Shank Size	1" IN
Length	1-3/4" IN
Material	Steel

Compliance Information	
<input type="checkbox"/>	ARRA Compliant
<input type="checkbox"/>	BAA Compliant
<input type="checkbox"/>	RoHS Compliant
<input type="checkbox"/>	UL Compliant

Item Status:	Active
Standard Qty:	1

Minerallac Company
Tel: 800-927-3293
Fax: 800-824-8942
www.minerallac.com

WARRANTY DISCLAIMER The information, data and recommendations contained herein may not be all inclusive or specific to your situation, and should only be used as a guide. The information is furnished upon the condition that the person receiving it shall make his/her own determination of the suitability of the product for his/her particular use and on condition that they assume the risk of the use thereof.

With respect to this publication and the product related thereto, except otherwise expressly provided by Manufacturer in writing, MANUFACTURER MAKES NO EXPRESS OR IMPLIED WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR ANY OTHER EXPRESS OR IMPLIED WARRANTY.

Remedy/Liability Limits The exclusive remedy for losses or damages resulting from this publication or the related product (including claims based on contract, negligence, strict liability or other legal theories) shall be limited to, at Manufacturer's sole election, one of the following: 1. Refund of purchase price paid by buyer or user for product bought, or 2. Replacement of amount of product used.

Manufacturer shall not be liable for losses or damages resulting from use of this publication or handling or use of this product, IN NO CASE SHALL MANUFACTURER BE LIABLE FOR CONSEQUENTIAL OR INCIDENTAL DAMAGES OR LOSSES, INCLUDING WITHOUT LIMIT, HEALTH RELATED DAMAGES OR INJURIES, OR LOST PROFITS.

The terms of this Warranty Disclaimer and Remedy/Liability Limits cannot be varied by any written or verbal statements or agreements. No employee or sales agent of Manufacturer or the seller is authorized to vary or exceed the terms of this Warranty Disclaimer or Limitation of Remedies in any manner.