



[Home \(Http://www.westgatemfg.com/\)](http://www.westgatemfg.com/) > LSL-4FT-40W-40K-D

# LSL-4FT-40W-40K-D



## OVERVIEW



### Technical Specifications:

- :: Strip line cover
- :: White finish
- :: Housing: Steel base with powder coating
- :: Lens: Frosted diffuse PC lens
- :: Ceiling-mounted
- :: Same footprint as traditional 2-lamp strip lights
- :: Power: 40W
- :: Voltage: 120~277V AC, 50/60Hz
- :: Chip: Samsung
- :: Dimmable 0~10V
- :: CRI: >80
- :: IP Rating: IP20
- :: Mounting: Surface mount, wall mount or suspended
- :: 5 years warranty

## FEATURES:



Tweet <http://twitter.com/share> Share

## DOWNLOADS

**SPEC SHEET**



LSL-4FT-40W-40K-D (<http://www.westgatemfg.com/import/westgateimages/documents/SPEC/LSL-4FT-40W-D SPEC SHEET.pdf>)

**CONTACT**

Westgate MFG Inc  
2462 E. 28th St.,  
Vernon, CA 90058

**Toll Free Tel:** 877-805-2252

**Toll Free Fax:** 877-809-2252

**International Tel:** +1323-826-9490

Opening Hours: 7:30AM to 4:30PM PST

Email: (<mailto:Info@westgatemfg.com>)[Info@westgatemfg.com](mailto:Info@westgatemfg.com)

(<mailto:Info@westgatemfg.com>)

We Love Hearing From You,

(<mailto:Info@westgatemfg.com>) (<mailto:Info@westgatemfg.com>)

Send Your Product & Service Feedbacks Directly To Westgate Management By Emailing: [Feedback@Westgatemfg.Com](mailto:Feedback@Westgatemfg.Com) (<mailto:Feedback@Westgatemfg.Com>)

**GET IN TOUCH WITH US**

Send

**QUICK LINKS**

- [➔ About Us \(http://www.westgatemfg.com/abouts\)](http://www.westgatemfg.com/abouts)
- [➔ Terms & Conditions \(http://www.westgatemfg.com/terms-and-condition\)](http://www.westgatemfg.com/terms-and-condition)
- [➔ Contact Us \(http://www.westgatemfg.com/contacts\)](http://www.westgatemfg.com/contacts)
- [➔ Privacy Policy \(http://www.westgatemfg.com/privacy-policy-cookie-restriction-mode\)](http://www.westgatemfg.com/privacy-policy-cookie-restriction-mode)

**NEWSLETTER**

Subscribe to the WESTGATE mailing list to receive updates on new arrivals, special offers and other discount information.

[Terms Of Use \(http://www.westgatemfg.com/terms-and-condition\)](http://www.westgatemfg.com/terms-and-condition)

[Privacy Policy \(http://www.westgatemfg.com/privacy-policy-cookie-restriction-mode\)](http://www.westgatemfg.com/privacy-policy-cookie-restriction-mode)

[Support \(http://www.westgatemfg.com/customer/account/login\)](http://www.westgatemfg.com/customer/account/login)

**WESTGATE** (<http://www.westgatemfg.com/>)

© 2017 WestGate Manufacturing. All Rights Reserved.