

5WMNT-1C

Mini SDX Wall-Mount Fiber Enclosure, empty, no lock



UPC Code : 078477824962

Country Of Origin : Mexico

To meet the demands of the Internet of Things (IoT), fog computing, and micro data center environments, the award-winning Leviton Opt-X SDX Mini Wall-Mount Fiber Optic Enclosure expands networking possibilities in a wide range of applications and environments. The space-saving footprint enables applications ranging from traditional telecommunications room patching in an enterprise setting to the implementation of small-scale edge data centers. It provides a compact, zero-RU patching field with a range of mounting options including wall-mount, surface-mount, DIN-rail, and even cubicle walls.

The Mini Wall-Mount Enclosure also allows for more flexibility in traditional inter-connect or cross-connects between cable and active equipment while using minimum wall space. Its features and design allow for easy field termination of fiber connectors, splicing, or pre-terminated plug-and-play solutions.

Features and Benefits

- Enclosure accommodates up to 24 fibers (using LC), 12 fibers (using SC), and 6 ports (for copper)
- Accepts SDX Precision-Molded Adapter Plates and SDX MTP Cassette for multiple solution capabilities
- Removable cable entry/exit grommets allow for pre-terminated fiber trunk install, cable protection, and minimizes dust build up
- Constructed of 16-gauge steel for enhanced durability
- Optional key/lock kit secures the door for added physical security
- Optional 0RU mounting bracket and magnet solutions available
- Multiple application usage, including wall mount, 0RU in rack/cabinet, ladder rack, workstation, cubicle, and within an enclosure (using adhesive-based tapes or magnets)

SPECIFICATION SUBMITTAL

JOB NAME: <input style="width: 95%; height: 20px;" type="text"/>	CATALOG NUMBERS: <input style="width: 60%; height: 20px;" type="text"/> <input style="width: 35%; height: 20px;" type="text"/>	
JOB NUMBER: <input style="width: 95%; height: 20px;" type="text"/>	<input style="width: 60%; height: 20px;" type="text"/>	<input style="width: 35%; height: 20px;" type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):
+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·
FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-
1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:
www.leviton.com/international/contacts/

