



MCR
SAFETY

Mossy Oak Safety Glasses

Premium Series Specification Sheet

PRODUCT DESCRIPTION:

MCR Safety® and Mossy Oak® Brand Camo have teamed up to bring you an amazing line up of Shadow Grass® Blades® gloves and glasses. Shadow Grass® Blades® features a precise arrangement of individual blades of grass, whether windblown, broken or bent, onto a background of thatch consisting of lesser or dead grass, to create the perfect pure grass pattern. Carefully placed shadows from the main grass arranged atop the thatch, which incorporates light to dark spots as seen in nature, creates depth that gives Shadow Grass® Blades® a realistic 3D appearance. The USS Defense glasses feature a stylish design with co-injected TPR/polycarbonate temples and TPR nose pads for extreme comfort. The MOUD glasses meet or exceed ANSI Z87+ high impact standard and military ballistic high velocity standard.



FEATURES:

- Mossy Oak Shadow Grass Blades camo design
- Sleek Co-Injected TPR over polycarbonate temples
- Meets Military Ballistic High Velocity Standard
- MAX6™, MAX36™ or BossMan® Mirror lens coatings
- Polarized options available

TECHNICAL DATA FOR: MOUD117BZDC

Series	Mossy Oak	ANSI Z87+	Yes
Category	Safety Glasses	MIL - PRF - 31013	Yes
Anti-Fog	Yes		
Scratch Resistant	Yes		
Frame Material	Polycarbonate		
Packaging	Multicolor Gravity Feed		
Case Pack	144 pair	Case Weight	19.737 lb.
Case Dimensions	20.472 x 19.291 x 13.386	Made In	Taiwan

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
----------	---------------	---------------	--------------------	-------	--------------	---------------	----------------

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2019 MCR Safety - All Rights Reserved



MCR
SAFETY

Mossy Oak Safety Glasses

Premium Series Specification Sheet

Item No:	Lens Options:	Lens Coating:	Scratch Resistant:	VLT%:	Frame Color:	Temple Color:	Temple Sleeve:
MO110	Clear	Duramass Hard Coat	Yes	90	Mossy Oak	Mossy Oak	Black
MO112	Gray	Duramass Hard Coat	Yes	13	Mossy Oak	Mossy Oak	Black
MO114	Amber	Duramass Hard Coat	Yes	80	Mossy Oak	Mossy Oak	Black
MO117	Silver Mirror	Duramass Hard Coat	Yes	13	Mossy Oak	Mossy Oak	Black
MO119	I/O Clear Mirror	Duramass Hard Coat	Yes	36	Mossy Oak	Mossy Oak	Black
MO11B	Brown	Duramass Hard Coat	Yes	13	Mossy Oak	Mossy Oak	Black
MO11V	Vermillion	Duramass Hard Coat	Yes	55	Mossy Oak	Mossy Oak	Black
MODL110	Clear	Duramass Hard Coat	Yes	90	Mossy Oak	Black	Black
MODL112	Gray	Duramass Hard Coat	Yes	13	Mossy Oak	Black	Black
MODL114	Amber	Duramass Hard Coat	Yes	80	Mossy Oak	Black	Black
MODL117	Silver Mirror	Duramass Hard Coat	Yes	13	Mossy Oak	Black	Black
MOUD110PF	Clear	MAX6 Anti-Fog	Yes	90	Mossy Oak	Mossy Oak	Black
MOUD112PF	Gray	MAX6 Anti-Fog	Yes	13	Mossy Oak	Mossy Oak	Black
MOUD114PF	Amber	MAX6 Anti-Fog	Yes	80	Mossy Oak	Mossy Oak	Black
MOUD117BZDC	Black Mirror	Polarized MAX36 Dual Coating	Yes	13	Mossy Oak	Mossy Oak	Black
MOUD118BZDC	Blue Diamond Mirror	Polarized MAX36 Dual Coating	Yes	13	Mossy Oak	Mossy Oak	Black
MOUD11BPF	Brown	MAX6 Anti-Fog	Yes	13	Mossy Oak	Mossy Oak	Black

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2019 MCR Safety - All Rights Reserved