



2-head Security Light with PIR Sensor (Bronze)

1800 lm | 120VAC | Model 51402241 | Part SC-20-840-SV-OS-BZ

- > Energy Saving 20 Watt Integrated LED
- > Save up to \$220 over the life of the fixture
- > Cool White 4000K CCT
- > With PIR Sensor
- > Tool Free Adjustability
- > Lasts 45 years* or 50,000 Hours Continuous Use
- > 5 Year Limited Warranty



SPECIFICATIONS

Model	51402241
Part	SC-20-840-SV-OS-BZ
Description	2-head Security Light with PIR Sensor (Bronze)
Input Voltage (VAC)	120
Wattage	20
Dimmability	NA
Average Rated Life¹	50,000 hours
Typical Lumens²	1800
CCT³	4000K
Location Rating	UL Wet
CRI⁴	80
Beam Angle	67°
Operating Temperature	Min -13°F (-25° C), Max 113°F (45° C)
Power Factor	>0.9
R9	-5
DUV	0.00075
CBCP	1500
Operating Frequency (Hz)	60

1 Hours lifetime with 70% lumen maintenance
 2 Thermally stable typical lumens (±10%)
 3 Thermally stable CCT (±10%)
 4 Color rendering index/Ra

ETI

LED lighting facts
A Program of the U.S. DOE

Light Output (Lumens)	1800
Watts	20
Lumens per Watt (Efficacy)	90
Color Accuracy	
Color Rendering Index (CRI) 80	
Light Color	
Correlated Color Temperature (CCT) 4000 (Bright White)	
Warm White	Bright White
2700K	3000K
4500K	6500K

All results are according to IESNA LM-79-2008, Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: 5BAM-IBK322 (11/9/2017)
 Model Number: 51402241(##=41-50)
 Type: Luminaire - Directional

TO ORDER:
www.ETiSSL.com
 Call: 1.855.ETi.SSLI
 1.855.384.7754





2-head Security Light with PIR Sensor (Bronze)

1800 lm | 120VAC | Model 51402241 | Part SC-20-840-SV-OS-BZ

SHIPPING INFORMATION

Model	51402241
Part	SC-20-840-SV-OS-BZ
UPC	849489009964
Product Dimensions (L x W x H in.)	6.89 x 4.53 x 5.51
Product Dimensions (L x W x H cm.)	17.5 x 11.5 x 14.0
Product Weight (lbs.)	2.03
Inner Carton Quantity	N/A
Inner Carton Bar Code	N/A
Inner Carton Dimensions (L x W x H in.)	N/A
Inner Carton Dimensions (L x W x H cm.)	N/A
Inner Carton Weight (lbs)	N/A
Master Carton Quantity	6
Master Carton Bar Code	50849489009969
Master Carton Dimensions (L x W x H in.)	21.81 x 18.35 x 7.01
Master Carton Dimensions (L x W x H cm.)	55.4 x 46.6 x 17.8
Master Carton Weight (lbs)	17.37
Pallet Quantity	360

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, Please see www.ETiSSL.com/fcc15b

TO ORDER:
www.ETiSSL.com
Call: 1.855.ETi.SSLI
1.855.384.7754

ETi Solid State Lighting, Inc.
720 Corporate Woods Parkway
Vernon Hills, IL 60061
Phone: 855.384.7754
Fax: 847.383.6256