



Lotus
LED
Lights



Type IC, Air-Tight, Wet & Plenum

DESCRIPTION

4" Round Recessed LED With Integral Driver In Connection Box
Commercial Grade Quality With Architectural Design


FEATURES & BENEFITS

2" Deep - Install Where Ceiling Space Is Limited
Type IC Rated - No Housing Required
CRI 90+ for True Color Rendering
Fast & Easy To Install - Save On Labor
Driver Inside Connection Box - No Junction Box Needed
Armored Cable & Metal Connectors - Open Plenum Rated

MOUNTING

Cut Hole In Ceiling And Snap Fixture In Opening With Attached Spring Clips. Ceiling Clearance Required: 2"

DIMENSIONS: ID 4" OD 5" Cut Out 4" to 4 1/4"



120V TRIAC Dimmable Driver Included



Optional 120V-347V Driver 0-10V Dimmable



Order Separately as
Cat # LLL-LD1535TR

ORDERING GUIDE Example: **LL4RR - 30K - WH**

	CCT	Trim Finish	
LL4RR	-	-	
2700K	27K	WH	White
3000K	30K	BK	Black
4000K	40K		

LL4RR

4" Round Regressed 2nd Gen Plenum LED 14.5W

Project: _____

Location: _____

Cat #: _____ Qty: _____

Notes: _____

SPECIFICATION	
Applications	Recessed Ceiling Mount
Energy Used	14.5 W
Color Temperature	2700 3000 4000
Light Output	950 1000 1020
Halogen Equivalent	90 W
Beam Angle	90°
CRI	90 +
Default Driver Input	120V AC Triac Dimmable
Optional Driver Input	120V-347V AC 0-10V Dimmable
Power Factor	0.95
Approved Location	Insulated Ceilings, Open Plenum, Wet
IP Rating	IP 54
Air Tight	Yes
Ambient Temperature	-40°F (-40°C) to +104°F (+40°C)
Projected Life	70% Light Output at 50,000 Hours
Certification	cULus, Energy Star, T24
Warranty	10 Year on Residential 5 Year on Commercial Applications

AVAILABLE TRIMS



White



Black

ACCESSORIES

Sold Separately



Armored Low Voltage Extensions
10ft - cat # **MEC10**
FT6 / CMP rated. Max 40 ft Allowed



Flat Rough-In Plates - cat # **RIP4**



Flanged Rough-In Plate - cat # **FRP4**



Goof Ring OD 5 3/4"
White cat # **GR4** Black cat # **GR4-BK**

COMPLIANCE



**Type IC
Air-Tight
Open Plenum**

Lotus LED Lights USA

www.LotusLEDLights.com

Lotus LED Lights CANADA

250 H Street # 301, Baine WA 98230 tel 360-200-5500

800-15355 24 Ave Box 200, Surrey BC V4A 2H9 tel 604-538-3090

Warehouses: Hainesport NJ, Naples FL, Dallas TX, Las Vegas NV, Lynnwood WA

Delta BC & Mississauga ON